

## Product data sheet

### Characteristics

# NSYTBS241910H

Thalassa, ABS box IP66 IK07 RAL7035  
 Int.H225W175D100 Ext.H241W194D105  
 Opaque cover H40



### Main

Range	Thalassa
Product name	Thalassa TBS
Device application	Multi-purpose
Category	Industrial box
Height	241 mm
Width	194 mm
Depth	107 mm
Internal height	225 mm
Internal width	175 mm
Internal depth	100 mm
Enclosure mounting	Wall mounted
Device composition	1 body 1 cover 4 cover screw
Body type	One piece moulded
Type of front cover	High plain cover
Cover fixing	Plastic screws
Lock type	Captive screw flat outside sealed area
Removable parts	Cover by captive screws

### Complementary

Material	ABS (acrylonitrile butadiene-styrene)
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product certifications	TÜV
Electrical insulation class	Class II
IP degree of protection	IP66 conforming to NEMA 4.4X
IK degree of protection	IK07 conforming to IEC 62262
Glow wire resistance	650 °C conforming to IEC 60695-2-11
Ambient air temperature for storage	-15...40 °C
Operating temperature	-25...60 °C
Net weight	0.72 kg

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12 cm
Package 1 Width	20 cm
Package 1 Length	25.5 cm
Package 1 Weight	696 g
Unit Type of Package 2	CAR
Number of Units in Package 2	9

Package 2 Height	40 cm
Package 2 Width	40.5 cm
Package 2 Length	60 cm
Package 2 Weight	7.146 kg
Unit Type of Package 3	P12
Number of Units in Package 3	108
Package 3 Height	136 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	94 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------