

Product data sheet

Characteristics

PDL354PBDMUN-VW

PDL Iconic, dimmer, 300M, universal, PB,
ControlLink, 300 W, Vivid White



Main

Range	PDL Iconic
Product or component type	Dimmer
Device presentation	Mechanism
Colour tint	Vivid white (VW)
Type of packing	Box
Load type	Incandescent lamp - 300 W Medium voltage halogen lamp - 300 W Low voltage halogen lamp with iron core transformer - 300 W Dimmable fluocompact lamp - 200 W Dimmable LED lighting driver - 200 W Dimmable fluorescent ballast - 200 W
Number of terminals	3

Complementary

Range compatibility	PDL Iconic
Control type	Push-button ControlLink
Fixing mode	Clip-in
Surface finish	Glossy
Ambient air temperature for storage	0...60 °C
Dimmer control	Push type
[Ie] rated operational current	1.2 A
[Ue] rated operational voltage	220...240 V AC 50 Hz 10 W
Function available	Brightness adjustment
Protection type	Short-circuit
Operating distance	30 mm
Connections - terminals	Screw terminal
Screwdriver shape	Square drive no 1 (SQ1) Phillips
Local signalling	LED indicator (warm white)
Material	PC (UL94 V-2): top PC MAS056 (UL94 V-2): bottom
Height	23.5 mm
Width	23.5 mm
Depth	42 mm
Embedding depth	39 mm

Environment

Derating factor	1 deviceswithout derating 2 deviceswith derating factor 3 deviceswith derating factor 4 deviceswith derating factor 5 deviceswith derating factor 6 deviceswith derating factor
Standards	AS/NZS 60669.2.1

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information