

## Product data sheet

### Characteristics

# PDL354PBDMUN-VW

## Module Universal LED Dimmer PushButton, Iconic, 300W ControlLink, 300 Series

### Main

Range	PDL Iconic
Product or component type	Dimmer
Device presentation	Mechanism
Type of packing	Box
Load type	Incandescent lamp - 300 W Medium voltage halogen lamp - 300 W Low voltage halogen lamp with iron core transformer - 300 W Dimmable fluocompact lamp - 200 W Dimmable LED lighting driver - 200 W Dimmable fluorescent ballast - 200 W
Number of terminals	3

### Complementary

Range compatibility	PDL Iconic
Control type	Push-button ControlLink
Fixing mode	Clip-in
Surface finish	Glossy
Ambient air temperature for storage	0...60 °C
Dimmer control	Push type
[Ie] rated operational current	1.2 A
[Ue] rated operational voltage	220...240 V AC 50 Hz 10 W
Function available	Brightness adjustment
Protection type	Short-circuit
Operating distance	30 m
Connections - terminals	Screw terminal
Screwdriver shape	Square drive no 1 (SQ1) Philips
Local signalling	LED indicator (warm white)
Material	PC (UL94 V-2): top PC MAS056 (UL94 V-2): bottom
Height	23.5 mm
Width	23.5 mm
Depth	42 mm
Embedding depth	39 mm

### Environment

Derating factor	1 devices 300 W without derating 2 devices 300 W with derating factor 3 devices 250 W with derating factor 4 devices 200 W with derating factor 5 devices 150 W with derating factor 6 devices 100 W with derating factor
Standards	AS/NZS 60669.2.1

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.9 cm
Package 1 Width	6.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	50 g
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	13 cm
Package 2 Width	9.6 cm
Package 2 Length	15.2 cm
Package 2 Weight	386 g

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	3