

# PDL56C320RCD30LEGY

## RCD Protected Socket, 20A, 240V, 3-Round Pin, 2-Gang, Grey



### Main

|                           |                                |
|---------------------------|--------------------------------|
| Range of product          | 56 Series™                     |
| Product or component type | Residual current device switch |
| Control type              | Push-button                    |

### Complementary

|                                       |                 |
|---------------------------------------|-----------------|
| Material                              | Plastic         |
| Colour tint                           | Grey            |
| Surface finish                        | Gloss           |
| Installation direction                | Vertical        |
| Width                                 | 95 mm           |
| Height                                | 191 mm          |
| Rated current                         | 20 A            |
| [Ue] rated operational voltage        | 230/240 V       |
| Network frequency                     | 50 Hz           |
| Network number of phases              | 1 phase         |
| Number of gangs                       | 2 gangs         |
| Pin number                            | 3               |
| Device composition                    | Round pin       |
| Mounting mode                         | Surface mounted |
| Fixing center                         | 84 x 180 mm     |
| IP degree of protection               | IP66            |
| Ambient air temperature for operation | -10...40 °C     |
| Quantity per set                      | Set of 2        |
| Type of packing                       | Carton          |

### Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Weight             | 0.504 kg |
| Package 1 Height             | 7 cm     |
| Package 1 width              | 9.5 cm   |
| Package 1 Length             | 19 cm    |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product                         |
| REACH Regulation           | <a href="#">REACH Declaration</a>             |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a> |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>                           |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a> |