

## Product data sheet

### Characteristics

# PDL625C31WH

3 Speed "No Hum" Capacitor Ceiling Sweep  
Fan Speed Controller; 1uF & 2uF, White



### Main

Range of product	600 Series
Product or component type	Switch


### Complementary

Control type	Rotary knob
Material	PC (polycarbonate)
Colour tint	White
Surface finish	Gloss
Installation direction	Vertical
Length	118 mm
Width	74 mm
[Ue] rated operational voltage	230/240 V
Network frequency	50 Hz
Network number of phases	1 phase
Number of gangs	1 gang
Number of poles	1
Mounting mode	Surface mounted
Fixing center	84 mm
Cable cross section	2 x 2.5 mm <sup>2</sup> 4 x 1.5 mm <sup>2</sup>
Quantity per set	Set of 1
Type of packing	Carton

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7 cm
Package 1 Width	8 cm
Package 1 Length	12 cm
Package 1 Weight	0.141 kg

### Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
-------------------	--