

Product data sheet

Characteristics

PDL634LMWH

Dimmer Control Module; 20 - 450W, Leading Edge Phase Control, White



Main

Range of product	600 Series
Product or component type	Switch
Dimmer control	Rotary


Complementary

Material	PC (polycarbonate)
Colour tint	White
Surface finish	Gloss
Installation direction	Vertical
Length	23 mm
Width	23 mm
Rated current	20 A 16 AX
[Ue] rated operational voltage	220/240 V
Network frequency	50 Hz
Power range	20 W 450 W
Load interrupting current	0.18 A 0.1 A
Motor M-rating AS3133	M60
Network number of phases	1 phase
Number of gangs	1 gang
Number of poles	1
Mounting mode	Front
Ambient air temperature for operation	0...40 °C
Quantity per set	Set of 10
Type of packing	Carton

Packing Units

Package 1 Weight	42.000 g
Package 1 Height	40.000 mm
Package 1 width	52.000 mm
Package 1 Length	80.000 mm

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
-------------------	--