

Product data sheet

Characteristics

PDL634LMWH

Dimmer Control Module; 20 - 450W, Leading Edge Phase Control, White



Main

Range of product	600 Series
Product or component type	Switch
Dimmer control	Rotary

Complementary

Material	PC (polycarbonate)
Colour tint	White
Surface finish	Gloss
Installation direction	Vertical
Length	23 mm
Width	23 mm
Rated current	20 A 16 AX
[Ue] rated operational voltage	220/240 V
Network frequency	50 Hz
Power range	20 W 450 W
Load interrupting current	0.18 A 0.1 A
Motor M-rating AS3133	M60
Network number of phases	1 phase
Number of gangs	1 gang
Number of poles	1
Mounting mode	Front
Ambient air temperature for operation	0...40 °C
Quantity per set	Set of 10
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4 cm
Package 1 Width	5.2 cm
Package 1 Length	8 cm
Package 1 Weight	42 g

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

EU RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)  [EU RoHS Declaration](#)