



Main

Range	EasyPact
Product name	EasyPact TVS
Product or component type	Contactor
Device short name	LC1E
Contactor application	Resistive load Motor control
Utilisation category	AC-3 AC-1
Poles description	3P
Power pole contact composition	3 NO
[Ue] rated operational voltage	Power circuit: ≤ 690 V AC 50/60 Hz
[Ie] rated operational current	25 A (at <60 °C) at ≤ 440 V AC-3 for power circuit 36 A (at <60 °C) at ≤ 440 V AC-1 for power circuit
Motor power kW	5.5 kW at 220...230 V AC 50/60 Hz 11 kW at 380...400 V 11 kW at 415 V 11 kW at 440 V 15 kW at 500 V 15 kW at 660...690 V
Control circuit type	AC at 50 Hz wide range
[Uc] control circuit voltage	220 V AC 50 Hz
Height	74 mm
Width	45 mm
Depth	85 mm
Net weight	0.36 kg
Colour	Grey (RAL 7011)

Complementary

Auxiliary contact composition	1 NO
[Uimp] rated impulse withstand voltage	6 kV coil not connected to the power circuit conforming to IEC 60947
[Ui] rated insulation voltage	690 V conforming to IEC 60947-4-1
Overvoltage category	III
Irms rated making capacity	250 A at 440 V AC for power circuit conforming to IEC 60947-4-1
Rated breaking capacity	200 A at 440 V for power circuit conforming to IEC 60947
[Icw] rated short-time withstand current	240 A 40 °C - 10 s for power circuit 120 A 40 °C - 60 s for power circuit 50 A 40 °C - 600 s for power circuit
Associated fuse rating	40 A gG at ≤ 690 V coordination type 1 for power circuit 10 A gG at ≤ 690 V for signalling circuit
Average impedance	2.5 mOhm - Ith 36 A 50 Hz for power circuit
Power dissipation per pole	1.6 W AC-3 3.2 W AC-1
Control circuit voltage limits	Drop-out: 0.3...0.6 Uc at 50 Hz (at <55 °C) Operational: 0.7...1.25 Uc at 50 Hz (at <55 °C)
Operating time	12...22 ms on closing 4...19 ms on opening
Mechanical durability	10 Mcycles
Maximum operating rate	1800 cyc/h 60 °C

Inrush power in VA	95 VA 50 Hz cos phi 0.75 (at 20 °C)
Hold-in power consumption in VA	8.5 VA 50 Hz cos phi 0.3 (at 20 °C)
Heat dissipation	2...3 W for control circuit
Minimum switching current	5 mA for signalling circuit
Minimum switching voltage	17 V for signalling circuit
Insulation resistance	> 10 MOhm for signalling circuit
Electrical durability	1.2 Mcycles AC-3 0.35 Mcycles AC-1
Mounting support	Plate DIN rail
Connections - terminals	Control circuit: screw clamp terminals 1 1...4 mm ² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 1...4 mm ² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 1 1...4 mm ² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 2 1...2.5 mm ² - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 1 1...6 mm ² - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 2 1...4 mm ² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 1...4 mm ² - cable stiffness: solid Control circuit: screw clamp terminals 2 1...4 mm ² - cable stiffness: solid Power circuit: screw clamp terminals 1 1.5...6 mm ² - cable stiffness: solid Power circuit: screw clamp terminals 2 1.5...6 mm ² - cable stiffness: solid
Recommended tightening torque	Control circuit: 1.2 N.m Power circuit: 1.5 N.m
Max tightening torque	Control circuit: 1.4 N.m Power circuit: 1.7 N.m

Environment

Standards	IEC 60947-5-1 IEC 60947-4-1
Product certifications	EAC
IP degree of protection	IP20 conforming to IEC 60529
Protective treatment	TH conforming to IEC 60068
Pollution degree	3
Ambient air temperature for operation	-5...55 °C
Ambient air temperature for storage	-60...80 °C
Permissible ambient air temperature around the device	-20...70 °C at U _c
Operating altitude	3000 m without derating
Fire resistance	850 °C conforming to IEC 60695-2-1
Mechanical robustness	Vibrations contactor open: 1.5 Gn, 5...300 Hz Vibrations contactor closed: 3 Gn, 5...300 Hz Shocks contactor closed: 10 Gn for 11 ms Shocks contactor open: 6 Gn for 11 ms

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	354 g
Package 1 Height	8.5 cm
Package 1 width	5 cm
Package 1 Length	7.5 cm
Unit Type of Package 2	S02
Number of Units in Package 2	36
Package 2 Height	15 cm
Package 2 width	30 cm
Package 2 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins