

# Product data sheet

## Characteristics

# PDL681MT16WH

## 681MT16 PUSH BUTTON SW WH



### Main

|                           |             |
|---------------------------|-------------|
| Range of product          | 600 Series  |
| Product or component type | Switch      |
| Control type              | Push-button |

### Complementary

|                                |  |
|--------------------------------|--|
| Material                       | PC (polycarbonate)                                 |
| Colour tint                    | White  |
| Surface finish                 | Gloss  |
| Installation direction         | Vertical<br>Horizontal                             |
| Rated current                  | 16 AX<br>20 A                                      |
| [Ue] rated operational voltage | 250 V  |
| Network type                   | AC   |
| Motor M-rating AS3133          | M50  |
| Number of poles                | 1  |
| Cable cross section            | 2 x 2.5 mm <sup>2</sup><br>4 x 1.5 mm <sup>2</sup> |

### Packing Units

|                              |        |
|------------------------------|--------|
| Unit Type of Package 1       | PCE    |
| Number of Units in Package 1 | 1      |
| Package 1 Height             | 2.5 cm |
| Package 1 Width              | 7.5 cm |
| Package 1 Length             | 11 cm  |
| Package 1 Weight             | 26 g   |

### Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product                         |
| REACH Regulation           | <a href="#">REACH Declaration</a>             |
| EU RoHS Directive          | Compliant with Exemptions                     |
| Mercury free               | Yes   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| RoHS exemption information | <a href="#">Yes</a>                           |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a> |
| Circularity Profile        | <a href="#">End Of Life Information</a>       |