

## Product data sheet

### Characteristics

# PDL883WH

## 2-Way Switch With Grid and Clip ; 16A/16AX, 3-Gang, 1P, White

### Main

|                           |                   |
|---------------------------|-------------------|
| Range of product          | Modena 800 Series |
| Product or component type | Switch module     |
| Control type              | Rocker            |
| Colour tint               | White             |
| Quantity per set          | Set of 10         |
| Type of packing           | Carton            |

### Complementary

|                                |  |
|--------------------------------|--|
| Material                       | PC (polycarbonate)   |
| Surface finish                 | Glossy and matt  |
| Installation direction         | Horizontal   |
| Width                          | 124 mm   |
| Height                         | 85 mm  |
| Depth                          | 9 mm   |
| Rated current                  | 16 A<br>16 AX  |
| [Ue] rated operational voltage | 250 V  |
| Network type                   | AC   |
| Network number of phases       | 1 phase  |
| Number of gangs                | 3 gangs  |
| Mounting mode                  | Surface mounted  |
| Fixing center                  | 84 mm  |
| Cable composition              | 3 x 2.5 mm <sup>2</sup><br>6 x 1.5 mm <sup>2</sup><br>2 x 4 mm <sup>2</sup><br>9 x 1 mm <sup>2</sup> |
| Connector type                 | #2 Phillips/Slot Screw   |

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type of Package 1       | PCE     |
| Number of Units in Package 1 | 1       |
| Package 1 Height             | 8.5 cm  |
| Package 1 Width              | 12.4 cm |
| Package 1 Length             | 0.9 cm  |
| Package 1 Weight             | 100 g   |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

|                            |  |
|----------------------------|--|
| EU RoHS Directive          | Compliant with Exemptions              |
| Mercury free               | Yes                                    |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a> |
| RoHS exemption information | <a href="#">Yes</a>                    |