

Product data sheet

Characteristics

PDL925RWH

Back Entry Heavy Duty Cord Connector; 10A, White

Main

| | |
|---------------------------|--------------------|
| Range of product | 900 Series |
| Product or component type | Socket |
| Material | PC (polycarbonate) |
| Colour tint | White |

Complementary

| | |
|---------------------------------------|-----------------------------|
| Surface finish | Gloss |
| Width | 45 mm |
| Diameter | 45 mm |
| Rated current | 10 A |
| [Ue] rated operational voltage | 230/240 V |
| Network frequency | 50 Hz |
| Network number of phases | 1 phase |
| Pin number | 3 |
| Ambient air temperature for operation | -10...40 °C |
| Cable cross section | 0.75... 1.5 mm ² |
| Connector type | Screw terminals |
| Quantity per set | Set of 20 |
| Type of packing | Carton |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 5 cm |
| Package 1 Width | 5 cm |
| Package 1 Length | 5.5 cm |
| Package 1 Weight | 0.043 kg |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 20 |
| Package 2 Height | 12 cm |
| Package 2 Width | 15.3 cm |
| Package 2 Length | 19.4 cm |
| Package 2 Weight | 1.08 kg |
| Unit Type of Package 3 | CAR |
| Number of Units in Package 3 | 200 |
| Package 3 Height | 21.6 cm |
| Package 3 Width | 32.5 cm |

| | |
|------------------|-----------|
| Package 3 Length | 62.9 cm |
| Package 3 Weight | 11300.0 g |

Offer Sustainability

| | |
|----------------------------|--|
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant with Exemptions |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |