


Product data sheet

Characteristics

PDLP343HG

Pro Series, Grid USB Charger, Type A, 2.1A
240V 3-Gang



Main

Range	Pro Series
Product or component type	USB charger
[Ue] rated operational voltage	220/240 V AC 50 Hz
Integrated connection type	3 USB 2.0 type A 5 V DC, maximum load current: 2.1 A
Maximum load current with 2 outputs used simultaneously	4.5 A

Complementary

Device mounting	Flush
Device presentation	Mechanism with fixing frame
Surface finish	Matt Textured
Fixing mode	By screws
Type of packing	Polybag
Quantity per set	Set of 5
Ambient air temperature for operation	0...45 °C
Ambient air temperature for storage	-5...50 °C
Relative humidity	10...95 %
Material	PC (polycarbonate) PP (polypropylene) ABS (acrylonitrile butadiene-styrene)
Protection type	Short time short-circuit protection
Number of terminals	3 screw terminal
Screwdriver shape	Square drive no 1 (SQ1) Philips No 2
Clamping connection capacity	1 x 2.5...4 x 2.5 mm ² for rigid or stranded cable(s) 3 x 4 mm ² for rigid or stranded cable(s)
Wire stripping length	16 mm
Standards	AS/NZ 3112
Height	78 mm
Width	38 mm
Depth	38 mm
Embedding depth	35 mm
Net weight	0.094 kg

Environment

Product certifications	RCM
Electrical insulation class	Class II
IK degree of protection	IK08
IP degree of protection	IP21

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	7.8 cm
Package 1 Length	11.6 cm
Package 1 Weight	102.56 g

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes