

## Product data sheet

### Characteristics

# PDLWSW202LEGY

## Weather Protected Double Isolating Surface Switch; 20A, 2-Gang, Light Grey



### Main

Range of product	WP Series
Product or component type	Switch
Switch function	1-pole 2-way
Control type	Rocker
Material	PC (polycarbonate)
Colour tint	Light grey

### Complementary

Surface finish	Gloss
Installation direction	Horizontal
Width	84 mm
Height	84 mm
Depth	72 mm
Rated current	20 A 16 AX
Motor M-rating AS3133	M60
[Ue] rated operational voltage	250 V
Network frequency	50 Hz
Number of gangs	2 gangs
Mounting mode	Surface mounted
IP degree of protection	IP56
Product specific application	Suits WE1 or WE1S enclosures
Clamping connection capacity	2 x 2.5 mm <sup>2</sup> 4 x 1.5 mm <sup>2</sup>
Type of packing	Carton

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>