


Product data sheet

Characteristics

VDIB17766UWE

Actassi S-110 Connector RJ45 Keystone

Unshielded Cat 6 White bag x 1



Main

Range	Actassi
Product type	RJ45 network socket
Device presentation	Two piece design
Colour tint	Stuffer cap: transparent (ABS + PC) IDC cover: blue (ABS + PC) Connector housing: white (ABS + PC)
Wiring Colour configuration	568 A/B
Quantity per set	Set of 1

Complementary

[In] rated current	1.5 A at 25 °C
Voltage proof	1000 V AC/DC peak, between contacts
Contact resistance	20 mOhm
Insulation resistance	Initial insulation resistance: ≥ 500 MOhm at 100 V DC
AWG gauge	AWG 24...AWG 23
Durability	750 cycles
Coupling attenuation	≥ 35 dB at 30...100 MHz $\geq 75 - 20 \times \log(f)$ dB at 100...1000 MHz
Contact pins	8 pins of copper alloy and gold plated conforming to IEC 60603-7
Pulling force	50 N during 60 s
Transverse conversion loss	≥ 50 dB $\geq 68 - 20 \times \log(f)$ dB at 1...250000 kHz
Tool type	Punch down tool Quick termination tool
Cable outer diameter	0.00...0.00 M 0.9...1.1 mm
Compatible LAN cable types	UTP
Communication network category	6
Supported applications	1000BASE-T
Protocols	VoIP (Voice IP) PoE+ (Power over Ethernet)
Product compatibility	RJ45 plug
Transmission frequency	0...250 MHz
Type of footprint	S-110 keystone
Height	0.02 M 22 mm
Length	0.04 M 36 mm
Width	0.02 M 16 mm
Targeted region	Europe Asia Pacific. North America.

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Operational temperature range	-40...70 °C -40...70 °C
Climatic category	40/070/21 (21 days)
Flame retardance	UL94-V0 conforming to UL listed

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	3 cm
Package 1 Length	2 cm
Package 1 Weight	0.008 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile