

### Main

Range of product	Harmony XD2
Product or component type	Complete joystick controller
Device short name	XD2
Mounting diameter	22 mm
Bezel material	Chromium plated metal

### Complementary

[Ui] rated insulation voltage	500 V (pollution degree 3) conforming to IEC 60947-1 600 V (pollution degree 3) conforming to UL 508 600 V (pollution degree 3) conforming to CSA C22.2 No 14
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947-1
Operator position information	All positions
Notch per direction	1
Operator direction information	2 directions
Contacts type and composition	1 NO for time delayed
Short-circuit protection	10 A gG (gl) Neozed cartridge fuse conforming to IEC 60947-5-1
Connections - terminals	Captive screw clamp terminals, 2 x 1.5 mm <sup>2</sup> with or without cable end Captive screw clamp terminals, 1 x 0.5 mm <sup>2</sup> with or without cable end Captive screw clamp terminals, 1 x 2.5 mm <sup>2</sup> with or without cable end
Electrical durability	1000000 Cycles, AC-15 at 230 V, operating rate <3600 cyc/h, load factor: 0.5 conforming to IEC 60947-5-1 appendix C 1000000 Cycles, AC-15 at 127 V, operating rate <3600 cyc/h, load factor: 0.5 conforming to IEC 60947-5-1 appendix C 1000000 Cycles, DC-13 at 24 V, operating rate <3600 cyc/h, load factor: 0.5 conforming to IEC 60947-5-1 appendix C 1000000 Cycles, DC-13 at 48 V, operating rate <3600 cyc/h, load factor: 0.5 conforming to IEC 60947-5-1 appendix C 1000000 Cycles, DC-13 at 120 V, operating rate <3600 cyc/h, load factor: 0.5 conforming to IEC 60947-5-1 appendix C 1000000 cycles, AC-15 at 48 V, operating rate <3600 cyc/h, load factor: 0.5 conforming to IEC 60947-5-1 appendix C
Contact code designation	A600-Q600
Overvoltage category	Class I conforming to IEC 61140
Mechanical durability	1000000 cycles
Fixing center	30 x 85 mm
Return	without
Height	122 mm
Depth	40 mm
Net weight	0.115 kg
[Ie] rated operational current	0.27 A at 250 V, DC-13, Q300 conforming to IEC 60947-5-1 3 A at 240 V, AC-15, A300

## Environment

Standards	IEC 60947-5-1
Product certifications	CSA[RETURN]UL[RETURN]LROS (Lloyds register of shipping)
Protective treatment	TC
Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-25...70 °C
Vibration resistance	5 gn (f= 40...500 Hz) conforming to IEC 60068-2-6
Shock resistance	20 gn conforming to IEC 60068-2-27
IP degree of protection	IP66 conforming to IEC 60529

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	14.4 cm
Package 1 Length	3.8 cm
Package 1 Weight	132.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	48
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	6.666 kg

## Offer Sustainability

Packaging without single use plastic	Yes
Packaging made with recycled cardboard	Yes
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	1