

SMX3000RMHV2UNC

APC Smart-UPS X, Line Interactive, 3kVA,
Rack/tower convertible 2U, 208V-230V, 8x
C13+1x C19 IEC, Network card, Extended
runtime



Oversikt

Presentasjon	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Leveringstid	Usually in Stock

Teknisk informasjon

Main Input Voltage	208 V 230 V
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Other Output Voltage	208 V 220 V 240 V
Merkeeffekt i W	2700 W
Merkeeffekt VA	3000 VA
Produkt eller type komponent	Uninterruptible power supply (UPS)
Input Connection Type	BS1363A Britisk IEC 320 C20 Schuko CEE 7 / EU1-16P
Output connection type	8 IEC 320 C13 2 IEC Jumpers 1 IEC 320 C19
Antall rack-enhet	2U
Kabellengde	2,44 m
Antall kabler	1
Batteritype	Bly-syre batteri
Inkludert utstyr	CD with software Rack mounting support rails Smart UPS signalling RS-232 cable Temperature probe Brukermanual Web/SNMP management card

Batteri og levetid

Extended runtime	1
Number of battery filled slots	0
Number of battery free slots	0
Batterioopladingstid	3 t
Number of battery replacement quantity	1

Batterilevetid	3...5 år
Batteri ladekraft	245 W rated

Generelt

Antall effektmodul	2400
Number of power module filled slots	0
Number of power module free slots	0
Product web sub-family	Network card pre-installed
Overflødig	No

Fysisk

Farge	Sort
Høyde	8,5 cm
Bredde	43,2 cm
Dybde	66,7 cm
Vekt	37,32 kg
Montasjeplassering	Front
Mounting preference	Lower
Monteringsmetode	Rack-mounted
Two post mountable	0
USB kompatibel	Yes

Inngang

Toleranse forsyningsspenning	140...280 V
Nettverksfrekvens	50/60 Hz +/- 3 Hz automatisk gjenkjenning

Utgang

Harmonisk forvrengning	Mindre enn 5 %
Maximum configurable power in VA	3000 VA
Maximum configurable power in W	2700 W
Overføringstid	2-4 ms 6 ms typical : 10 ms maximum
UPS type	Line interactive
Wave type	Sine wave
Utgangsfrekvens	50/60 Hz +/- 3 Hz sync to mains

Overenstemmelse

Produktsertifikater	C- Tick[RETURN]CE[RETURN]EAC[RETURN]GOST[RETURN]IRAM[RETURN]VDE
Standarder	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Miljømessig

Akkustikknivå	55 dBA
Varmeavgivelse	184 Btu/t
Driftshøyde	0...10000 ft
Omgivelsestemperatur drift	0...40 °C
Omgivelsestemperatur for lagring	-15...45 °C
Storage altitude	0,00...15240,00 m
Relativ fuktighet	0...95 %
Storage Relative Humidity	0...95 %

Kommunikasjon og ledelse

Kontrollpanel	Multifunction LCD status and control console
Nødstop	Yes
Ledige plasser	0
Preinstalled device	Network management card 3 with environmental monitoring
Control panel	LED status display with on line : on battery : replace battery and overload indicators
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

Overspenningsbeskyttelse og filtrering

Surge energy rate	645 J
Noise suppression	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Forpakkingsinformasjon

Enhetstype pakke 1	PCE
Antall enheter i pakke 1	1
Pakke 1 Høyde	24,3 cm
Pakke 1 Bredde	59,6 cm
Pakke 1 Vekt	86,9 cm
Package 1 Weight	45,36 kg
Enhetstype pakke 2	PAL
Antall enheter i pakke 2	8
Pakke 2 Høyde	119 cm
Pakke 2 Bredde	100 cm
Pakke 2 Lengde	120 cm
Pakke 2 Vekt	382,4 kg
Antall enheter på en pall	2
Antall pallelag	4

Bærekraftig

Produktets miljøstatus	Green Premium miljømerket produkt
REACH-regelverk	 REACH-erklæring
EU RoHS-direktiv	Samsvar med unntak
Kvikksølvfri	Ja
Informasjon om RoHS-unntak	 Ja
Miljøinformasjon	 Produktmiljøprofil
Produktets livssyklus	 Informasjon Om Levetidsslutt
Optimalisert energieffektivitet	Energieffektivt produkt
Take-back	Take-back program available

Logistisk informasjon

Opprinnelsesland	PH
------------------	----

Garantiperiode

Garanti	3 years repair or replace (excluding battery) and 2 years for battery, optional extended warranties available, optional on-site warranties available
---------	--