

Dybde	44 mm
Vekt	0,455 kg
Klemmebeskrivelse ISO n°1	(13-14)NO (21-22)NC

Miljø

Støtmotstand	50 gn for 11 ms i samsvar med IEC 60068-2-27
Vibrasjonsmotstand	25 gn (f= 10...500 Hz) i samsvar med IEC 60068-2-6
IP-grad	IP66 conforming to IEC 60529
Ik beskyttelsesklasse	IK07 conforming to IEC 62262
Overspenningskategori	Klasse I i samsvar med IEC 61140 Klasse I i samsvar med NF C 20-030
Omgivelsestemperatur drift	-25...70 °C
Omgivelsestemperatur for lagring	-40...70 °C
Overflatebeskyttelse	TH
Produktsertifikater	CSA[RETURN]UL[RETURN]CCC
Standarder	IEC 60947-5-1 IEC 60947-5-1 UL 508 IEC 60204-1 CSA C22.2 No 14 CENELEC EN 50041 IEC 60204-1

Forpakkingsinformasjon

Enhetstype pakke 1	PCE
Antall enheter i pakke 1	1
Pakke 1 Høyde	4,5 cm
Pakke 1 Bredde	7,0 cm
Pakke 1 Vekt	12,8 cm
Package 1 Weight	464,0 g
Enhetstype pakke 2	S02
Antall enheter i pakke 2	18
Pakke 2 Høyde	15 cm
Pakke 2 Bredde	30 cm
Pakke 2 Lengde	40 cm
Pakke 2 Vekt	8,63 kg
Enhetstype pakke 3	PAL
Antall enheter i pakke 3	288
Pakke 3 Høyde	77,0 cm
Pakke 3 Bredde	60,0 cm
Pakke 3 Lengde	80,0 cm
Pakke 3 Vekt	144,804 kg

Bærekraftig

Produktets miljøstatus	Green Premium miljømerket produkt
REACH-regelverk	 REACH-erklæring
EU RoHS-direktiv	Proaktivt i samsvar (Produktet inngår ikke i EUs RoHS direktivet)
Kvikksølvfri	Ja
Informasjon om RoHS-unntak	 Ja
Produktets livssyklus	Ingen behov for spesifikke resirkuleringsprosedyrer

Logistisk informasjon


Opprinnelsesland	ID
------------------	----

Garantiperiode

Garanti

18 months


Dimensions



(1) 1 tapped entry Pg 13.5

Mounting with Cable Entry

Position of Cable Gland




(1) Recommended

(2) To be avoided


Wiring Diagram

2-pole NC + NO Snap Action




Characteristics of Actuation

Switch Actuation by 30° Cam



Functionnal Diagram



(P) Positive opening point

(A) Cam displacement

(1) NC contact with positive opening operation

(2) Closed

(3) Open

(4) Tripping

(5) Resetting