



Teknisk informasjon

Produktspekter	Harmony XB6
Produkt eller type komponent	Hode for signallamper
Produktkompatibilitet	Innebygget LED
Kortnavn utstyr	ZB6
Innfatningsmateriale	Plast
Montasjediometer	16 mm
Salg per udelelig kvantitet	1
Formen på varslingsenhetens hode	Rektangulær
Hette eller deksselfarge	Hvit

Komplementær

Bredde	24 mm
Høyde	18 mm
Dybde	33 mm
Vekt	0,015 kg

Miljø

Overflatebeskyttelse	TC
Omgivelsestemperatur for lagring	-40...70 °C
Omgivelsestemperatur drift	-25...70 °C
Beskyttelsesgrad mot elektrisk støt	Klasse II i samsvar med IEC 61140
IP-grad	IP65 i samsvar med IEC 60529
NEMA beskyttelsesgrad	NEMA 13 i samsvar med UL 50 NEMA 4 i samsvar med UL 50 NEMA 4X i samsvar med UL 50 NEMA 13 i samsvar med CSA C22.2 No 94 NEMA 4 i samsvar med CSA C22.2 No 94 NEMA 4X i samsvar med CSA C22.2 No 94
Standarder	IEC 60947-5-5 JIS C 852 UL 508 IEC 60947-1 CSA C22.2 No 14 JIS C 4520 IEC 60947-5-1
Produktsertifikater	GOST[RETURN]CCC[RETURN]UL[RETURN]CSA
Vibrasjonsmotstand	+/- 3 mm (f= 2...500 Hz) i samsvar med IEC 60068-2-6 5 gn (f= 2...500 Hz) i samsvar med IEC 60068-2-6
Støtmotstand	30 gn (varighet = 18 ms) for halvsinuskurve akselerasjon i samsvar med IEC 60068-2-27 50 gn (varighet = 11 ms) for halvsinuskurve akselerasjon i samsvar med IEC 60068-2-27

Forpakkingsinformasjon

Enhetstype pakke 1	PCE
Antall enheter i pakke 1	1
Pakke 1 Høyde	2,0 cm
Pakke 1 Bredde	10,0 cm
Pakke 1 Vekt	16,0 cm

Package 1 Weight	9,0 g
Enhetstype pakke 2	S01
Antall enheter i pakke 2	80
Pakke 2 Høyde	15,0 cm
Pakke 2 Bredde	15,0 cm
Pakke 2 Lengde	40,0 cm
Pakke 2 Vekt	896,0 g

Bærekraftig

REACH-regelverk	REACH-erklæring
REACH fri for SVHC	Ja
EU RoHS-direktiv	Proaktivt i samsvar (Produktet inngår ikke i EUs RoHS direktivet) EU RoHS-erklæring
Fri for giftige tungmetaller	Ja
Kvikksølvfri	Ja
Kinas RoHS-forskrift	Kinas RoHS-Erklæring
Informasjon om RoHS-unntak	Ja

Logistisk informasjon


Opprinnelsesland	FR
------------------	----

Garantiperiode

Garanti	18 months
---------	-----------

Rectangular Head for Pilot Light

Dimensions



Panel Cut-out

For Rectangular Head



Pushbuttons, Switches and Pilot Lights for Printed Circuit Board Connection

Front Panel Cut-out (Viewed from Installer's Side)



Printed Circuit Board Drillings (Viewed from Electrical Block Side)



A 24 mm/0.94 in. minimum for rectangular heads, 18 mm/0.71 in. minimum for square or circular heads

B 18 mm/0.71 in. minimum

(1) 6 x Ø 1.1 mm / 6 x Ø 0.04 in. holes.

(2) 1 x Ø 2.6⁰_{-0.2} mm / 1 x Ø 0.10⁰_{-0.008} in. hole for locating pin, only when using socket adaptor ZB6Y010.

(3) 1 x Ø 3.2⁰_{-0.2} mm / 1 x Ø 0.13⁰_{-0.008} in. hole for fixing of printed circuit board onto the front panel using body bracket ZB6Y011.
This hole must be drilled on the left-hand side, when heads are positioned at the normal angle. Fit a body bracket ZB6Y011 every 72 mm/2.83 in. maximum for cut-outs on 24 mm/0.94 in. centres (rectangular heads) and 54 mm/2.13 in. maximum for cut-outs on 18 mm/0.71 in. centres (square or circular heads).

General tolerances of the panel and printed circuit board: T1, T2: T1 + T2 = 0.3 mm/0.01 in. maximum.

Installation precautions:

Thickness of printed circuit board: 1.6 mm/0.06 in. minimum.

Mounting with Body Bracket

With socket adaptor ZB6Y010



(1) Head

(2) Nut

(3) Body

(4) Body bracket

(5) Contact block

(6) Socket adaptor

(7) Panel

(8) Printed circuit

Direct mounting without socket adaptor ZB6Y010



- (1) Head
- (2) Nut
- (3) Body
- (4) Body bracket
- (5) Contact block
- (6) Panel
- (7) Printed circuit