

Product data sheet

Characteristics

3MZ2-H1AUW

motor protection relay combined 3CT100 -
0.5..60 A - 100..240 V AC/DC



Main

Range of product	EOCR
Device short name	EOCR-3MZ2
Product or component type	Protection relay
Protection type	Overload, In > OC setting Underload, In < UC setting Locked rotor for starting, In > 2...8 times OC setting Locked rotor for running, In > 1.5...5 times OC setting Sensitivity to phase loss Phase unbalance, 10...50 % Earth fault, Ig > Ig setting Sensitivity to phase reverse
Product specific application	Motor protection
Network type	AC
Network frequency	50...60 Hz
Protection adjustment range	0.5...60 A
Tripping threshold	0.5...32 A (inverse and thermal) 0.5...60 A (definite) 0.03...10 A (definite) - earth fault current

Complementary

[Us] rated supply voltage	100...240 V AC/DC
Mounting support	35 mm DIN rail Panel
Contacts type and composition	1 NO (GR) 1 NO (OL)
Short-circuit and overload protection	By 4 A gG fuse
[Ue] rated operational voltage	600 V AC 50...60 Hz for power circuit conforming to UL 690 V AC 50...60 Hz for power circuit conforming to CSA 690 V AC 50...60 Hz for power circuit conforming to IEC 60947-4-1
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947-4-1
Reset	Manual reset Automatic reset 0.5...1200 s Electrical 0...1 s by interruption of power supply
Time delay type	D-Time: 0...200 s O-Time: 0.2...30 s (definite) O-Time: 1...30 class (inverse and thermal) U-Time: 0.5...30 s E-Time: 0.05...10 s Ed-Time: 0...30 s
Display type	7 segments LED Bar graph
Power consumption per relay	3 W
Connections - terminals	Control circuit: cable 2 x 1...1.5 mm ² flexible with cable end - M3 Control circuit: cable 2 x 1...1.5 mm ² flexible without cable end - M3 Control circuit: cable 1 x 1...2.5 mm ² flexible with cable end - M3 Control circuit: cable 1 x 1...2.5 mm ² flexible without cable end - M3
Tightening torque	Control circuit: 0.8...1.2 N.m on cable, 4.7 mm
Height	74.5 mm

Width	150 mm
Depth	155 mm
Net weight	0.893 kg

Environment

Standards	IEC 60947-4-1
Product certifications	UL
IP degree of protection	IP20 conforming to IEC 60529
Ambient air temperature for operation	-20...60 °C conforming to IEC 60947-4-1
Ambient air temperature for storage	-40...85 °C
Operating altitude	2000 m
Fire resistance	650 °C conforming to IEC 60695-2-12 960 °C conforming to UL 94
Shock resistance	15 gn for 11 ms conforming to IEC 60068-2-7
Vibration resistance	4 gn on panel mounting conforming to IEC 60068-2-6 2 gn on 35 mm DIN rail conforming to IEC 60068-2-6
Dielectric strength	2 kV 50...60 Hz in between case and circuit conforming to IEC 60255-5 1 kV 50...60 Hz in between contact conforming to IEC 60255-5 2 kV 50...60 Hz in between circuit conforming to IEC 60255-5
Surge withstand	6 kV conforming to IEC 61000-4-5
Electromagnetic compatibility	Resistance to radiated electromagnetic fields: 10 V/m level 3 conforming to IEC 61000-4-3 Resistance to electrostatic discharge: 8 kV air, 6 kV contact conforming to IEC 61000-4-2 Resistance to fast transient: 2 kV conforming to IEC 61000-4-4 Conducted RF disturbances: 10 V conforming to EN 61000-4-6 Conducted RF disturbances: class A conforming to EN 55011
[I _{th}] conventional free air thermal current	3 A for control circuit
Permissible current	250 V, 3 A AC

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------