



Osnovne informacije

Grupa proizvoda	TeSys TeSys Deca
Ime proizvoda	TeSys Deca
Tip proizvoda ili komponente	Pomoćni kontakti blok
Kratko ime uređaja	LADN
Kompatibilnost grupe proizvoda	TeSys D CAD[RETURN]TeSys D LC1D[RETURN]TeSys F LC1F[RETURN]TeSys F CR1F[RETURN]TeSys Deca CAD[RETURN]TeSys Deca LC1D
Lokacija za montiranje	Prednji deo
Raspored kontakata	2 NO
Contacts operation	Trenutno
[ue] nazivni radni napon	690 V AC 25...400 Hz
[ie] nazivna struja	6 A at 120 V AC-15 1,04 A at 690 V AC-15 0,55 A at 125 V DC-13 0,1 A at 600 V DC-13
[ui] nazivni napon izolacije	690 V u skladu sa IEC 60947-5-1 600 V u skladu sa UL 600 V u skladu sa CSA
[ith] dozvoljena termička struja u vazduhu	10 A (at 60 °C)
Standardi	UL 60947-5-1 CSA C22.2 No 60947-5-1 GB/T 14048.5 EN 50012
Sertifikacija proizvoda	CB[RETURN]UL[RETURN]CSA[RETURN]CCC[RETURN]IEC[RETURN]CE

Dopunske informacije

Irms nazivna moć uključenja	140 A AC conforming to IEC 60947-5-1 250 A DC conforming to IEC 60947-5-1
Dopustivo kratkotrajno opterećenje	100 A 60 °C 1 s 120 A 60 °C 500 ms 140 A 60 °C 100 ms
Tip zaštite	GG osigurač 10 A
Mehanička trajnost	30 miliona ciklusa
Minimalna struja preklapanja	5 mA
Minimalni napon preklapanja	17 V
Vreme nepreklapanja	1,5 Milisekundi pri isključenju bez preklapanja između NC i NO kontakta 1,5 milisekundi pri zatvaranju bez preklapanja između NC i NO kontakta
Otpornost izolacije	> 10 MOhm
Povezivanje - priključci	Vijčani priključni blokovi 1 kabl(ovi) 1...4 mm ² fleksibilni sa Vijčani priključni blokovi 1 kabl(ovi) 1...4 mm ² fleksibilni bez kablovskog završetka Vijčani priključni blokovi 2 kabl(ovi) 1...2,5 mm ² fleksibilni sa Vijčani priključni blokovi 2 kabl(ovi) 1...4 mm ² fleksibilni bez kablovskog završetka Vijčani priključni blokovi 1 kabl(ovi) 1...4 mm ² kruti bez kablovskog završetka Vijčani priključni blokovi 2 kabl(ovi) 1...4 mm ² kruti bez kablovskog završetka
Moment pritezanja	1,7 N.M - sa odvijačem matica Ø 6 mm 1,7 N.M - sa odvijačem Philips No 2 1,7 N.m - sa odvijačem pozidiv broj 2
Visina	48 mm
Širina	26 mm

Dubina	42 mm
Boja	Tamnosiva

Okruženje

Karakteristike životne sredine	Normalna sredina
Ip stepen zaštite	IP20 conforming to IEC 60529
Zaštitni tretman	TH u skladu sa IEC 60068
Temperatura okoline za skladištenje	-60...80 °C
Temperatura okoline za rad uređaja	-5...60 °C
Nadmorska visina za rad uređaja	3000 m

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2,800 cm
Package 1 Width	4,200 cm
Package 1 Length	5,200 cm
Package 1 Weight	34,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	2,800 cm
Package 2 Width	8,600 cm
Package 2 Length	25,600 cm
Package 2 Weight	342,000 g
Unit Type of Package 3	S03
Number of Units in Package 3	320
Package 3 Height	30,000 cm
Package 3 Width	30,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	11,452 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Usaglašeno  EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	18 meseci
-----------	-----------