



Osnovne informacije

Grupa proizvoda	TeSys Deca
Tip proizvoda ili komponente	Kontaktör
Kratko ime uređaja	LC1D
Primena kontaktora	Rezistivno opterećenje Upravljanje motorom
Kategorija upotrebe	AC-3 AC-4 AC-1 AC-3e
Broj polova	3P
[ue] nazivni napon	Kolo napajanja: ≤ 690 V AC 25...400 Hz Kolo napajanja: ≤ 300 V DC
[ie] nazivna struja	32 A (at <60 °C) at ≤ 440 V AC AC-3 for kolo napajanja 50 A (at <60 °C) at ≤ 440 V AC AC-1 for kolo napajanja 32 A (at <60 °C) at ≤ 440 V AC AC-3e for kolo napajanja
[Uc] control circuit voltage	24 V AC 50/60 Hz

Dopunske informacije

Snaga motora kw	7,5 kW at 220...230 V AC 50/60 Hz (AC-3) 15 kW at 380...400 V AC 50/60 Hz (AC-3) 15 kW at 415...440 V AC 50/60 Hz (AC-3) 18,5 kW at 500 V AC 50/60 Hz (AC-3) 18,5 kW at 660...690 V AC 50/60 Hz (AC-3) 7,5 kW at 400 V AC 50/60 Hz (AC-4) 7,5 kW at 220...230 V AC 50/60 Hz (AC-3e) 15 kW at 380...400 V AC 50/60 Hz (AC-3e) 15 kW at 415...440 V AC 50/60 Hz (AC-3e) 18,5 kW at 500 V AC 50/60 Hz (AC-3e) 18,5 kW at 660...690 V AC 50/60 Hz (AC-3e)
Snaga motora HP (UL / CSA)	2 Hp at 115 V AC 50/60 Hz for monofazne motors 5 Hp at 230/240 V AC 50/60 Hz for monofazne motors 10 Hp at 200/208 V AC 50/60 Hz for trofazne motors 10 Hp at 230/240 V AC 50/60 Hz for trofazne motors 20 Hp at 460/480 V AC 50/60 Hz for trofazne motors 25 hp at 575/600 V AC 50/60 Hz for trofazne motors
Kompatibilnost	LC1D
Sastav kontakta strujnog pola	3 NO
Prednja korica	Sa
[ith] dozvoljena termička struja u vazduhu	10 A (at 60 °C) for signalno kolo 50 A (at 60 °C) for kolo napajanja
Irms nazivna moć uključenja	140 A AC for signalno kolo conforming to IEC 60947-5-1 250 A DC for signalno kolo conforming to IEC 60947-5-1 550 A at 440 V for kolo napajanja conforming to IEC 60947
Nazivna prekidna moć	550 A at 440 V for kolo napajanja conforming to IEC 60947
[icw] kratkotrajna podnosiva struja kratkog spoja	260 A 40 °C - 10 s for kolo napajanja 430 A 40 °C - 1 s for kolo napajanja 60 A 40 °C - 10 min for kolo napajanja 138 A 40 °C - 1 min for kolo napajanja 100 A - 1 s for signalno kolo 120 A - 500 ms for signalno kolo 140 A - 100 ms for signalno kolo

Pripadajući osigurač	10 A gG for signalno kolo conforming to IEC 60947-5-1 63 A gG at ≤ 690 V coordination tip 1 for kolo napajanja 63 A gG at ≤ 690 V coordination tip 2 for kolo napajanja
Prosečna impedansa	2 mΩ - Ith 50 A 50 Hz for kolo napajanja
Snaga disipacije po polu	2 W AC-3 5 W AC-1 2 W AC-3e
[ui] nazivni napon izolacije	Kolo napajanja: 690 V u skladu sa IEC 60947-4-1 Kolo napajanja: 600 V CSA sertifikovano Kolo napajanja: 600 V UL sertifikovano Signalno kolo: 690 V u skladu sa IEC 60947-1 Signalno kolo: 600 V CSA sertifikovano Signalno kolo: 600 V UL sertifikovano
Kategorija prenapona	III
Stepen zaprljanosti	3
[uimp] nazivni podnosivi impulsni napon	6 kV u skladu sa IEC 60947
Nivo sigurnosne pouzdanosti	B10d = 1369863 ciklusa kontaktor sa nazivnim opterećenjem u skladu sa EN/ISO 13849-1 B10d = 20000000 ciklusa kontaktor sa mehaničkim opterećenjem u skladu sa EN/ISO 13849-1
Mehanička trajnost	15 miliona ciklusa
Električna trajnost	1,65 Miliona ciklusa 32 A AC-3 pri Ue ≤ 440 V 1,4 Miliona ciklusa 50 A AC-1 pri Ue ≤ 440 V 1,65 miliona ciklusa 25 A AC-3e pri Ue ≤ 440 V
Tip upravljačkog kola	AC pri 50/60 Hz standardno
Tehnologija kalema	Bez ugrađenog prigušivača
Ograničenje napona upravljačkog kola	0.3...0.6 Uc -40...70 °C propad napona AC 50/60 Hz 0.8...1.1 Uc -40...60 °C u radu AC 50 Hz 0.85...1.1 Uc -40...60 °C u radu AC 60 Hz 1...1.1 Uc 60...70 °C u radu AC 50/60 Hz
Udar na snagu u va	70 VA 60 Hz cos phi 0,75 (at 20 °C) 70 VA 50 Hz cos phi 0,75 (at 20 °C)
Snaga držanja u va	7,5 VA 60 Hz cos phi 0,3 (at 20 °C) 7 VA 50 Hz cos phi 0,3 (at 20 °C)
Disipacija toplote	2...3 W at 50/60 Hz
Vreme uključenja/isključenja	12...22 ms zatvaranje 4...19 ms otvaranje
Maksimalni radni ciklus	3600 ciklusa/h pri ≤60 °C
Povezivanje - priključci	Upravljačko kolo: vijčani priključni blokovi 1 1...4 mm ² - cable stiffness: fleksibilni bez kablovskog završetka Upravljačko kolo: vijčani priključni blokovi 2 1...4 mm ² - cable stiffness: fleksibilni bez kablovskog završetka Upravljačko kolo: vijčani priključni blokovi 1 1...4 mm ² - cable stiffness: fleksibilni sa kablovskim završetkom Upravljačko kolo: vijčani priključni blokovi 2 1...2,5 mm ² - cable stiffness: fleksibilni sa kablovskim završetkom Upravljačko kolo: vijčani priključni blokovi 1 1...4 mm ² - cable stiffness: jednožični bez kablovskog završetka Upravljačko kolo: vijčani priključni blokovi 2 1...4 mm ² - cable stiffness: jednožični bez kablovskog završetka Kolo napajanja: vijčani priključni blokovi 1 2,5...10 mm ² - cable stiffness: fleksibilni bez kablovskog završetka Kolo napajanja: vijčani priključni blokovi 2 2,5...10 mm ² - cable stiffness: fleksibilni bez kablovskog završetka Kolo napajanja: vijčani priključni blokovi 1 1...10 mm ² - cable stiffness: fleksibilni sa kablovskim završetkom Kolo napajanja: vijčani priključni blokovi 2 1,5...6 mm ² - cable stiffness: fleksibilni sa kablovskim završetkom Kolo napajanja: vijčani priključni blokovi 1 1,5...10 mm ² - cable stiffness: jednožični bez kablovskog završetka Kolo napajanja: vijčani priključni blokovi 2 2,5...10 mm ² - cable stiffness: jednožični bez kablovskog završetka
Moment pritezanja	Upravljačko kolo: 1,7 N.m - na vijčani priključni blokovi - sa odvijačem matica Ø 6 mm Upravljačko kolo: 1,7 N.m - na vijčani priključni blokovi - sa odvijačem Philips No 2 Kolo napajanja: 2,5 N.m - na vijčani priključni blokovi - sa odvijačem matica Ø 6 mm Kolo napajanja: 2,5 N.m - na vijčani priključni blokovi - sa odvijačem Philips No 2 Upravljačko kolo: 1,7 N.m - na vijčani priključni blokovi - sa odvijačem pozidiv broj 2 Kolo napajanja: 2,5 N.m - na vijčani priključni blokovi - sa odvijačem pozidiv broj 2

Sastav pomoćnog kontakta	1 NO + 1 NC
Tip pomoćnog kontakta	Tip mehanički povezani 1 NO + 1 NC u skladu sa IEC 60947-5-1 Tip preslikani kontakt 1 NC u skladu sa IEC 60947-4-1
Frekvencija signalnog kola	25...400 Hz
Minimalni napon preklapanja	17 V for signalno kolo
Minimalna struja preklapanja	5 mA for signalno kolo
Otpornost izolacije	> 10 MOhm for signalno kolo
Vreme nepreklapanja	1,5 Milisekundi pri isključenju između NC i NO kontakta 1,5 milisekundi pri zatvaranju između NC i NO kontakta
Nosači za montažu	Šina Ploča

Okruženje

Standardi	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 IEC 60335-1
Sertifikacija proizvoda	GL[RETURN]BV[RETURN]DNV[RETURN]LROS (Lloyds register of shipping) [RETURN]RINA[RETURN]UL[RETURN]CCC[RETURN]CSA[RETURN]GOST[RETURN]UKCA
Ip stepen zaštite	IP20 prednja strana u skladu sa IEC 60529
Zaštitni tretman	TH u skladu sa IEC 60068-2-30
Klimatska izdržljivost	U skladu sa IACS E10 izlaganje toploj i vlažnoj sredini U skladu sa IEC 60947-1 Annex Q category D izlaganje toploj i vlažnoj sredini
Dopustiva temperatura u okolini uređaja	-40...60 °C 60...70 °C sa promenom karakteristika
Nadmorska visina za rad uređaja	0...3000 m
Otpornost na vatru	850 °C u skladu sa IEC 60695-2-1
Otpornost na plamen	V1 u skladu sa UL 94
Mehanička robusnost	Vibracije kontaktor nije u radu (2 Gn, 5...300 Hz) Vibracije na kontaktor u radu (4 Gn, 5...300 Hz) Udara na kontaktor u radu (15 Gn za 11 ms) Udara kontaktor nije u radu (8 Gn za 11 ms)
Visina	85 mm
Širina	45 mm
Dubina	92 mm
Masa proizvoda	0,375 kg

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5,000 cm
Package 1 Width	9,200 cm
Package 1 Length	11,200 cm
Package 1 Weight	419,000 g
Unit Type of Package 2	S02
Number of Units in Package 2	20
Package 2 Height	15,000 cm
Package 2 Width	30,000 cm
Package 2 Length	40,000 cm
Package 2 Weight	8,634 kg
Unit Type of Package 3	P06
Number of Units in Package 3	320
Package 3 Height	75,000 cm
Package 3 Width	60,000 cm
Package 3 Length	80,000 cm
Package 3 Weight	145,500 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Usaglašeno EU RoHS Deklaracija
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Izjava o zaštiti okoliša	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Informacije O Kraju Radnog Veka
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.
Bez PVC	Da

Ugovorna garancija

Garancija	18 meseci
-----------	-----------

Dimensions



- (1) Including LAD 4BB
(2) Minimum electrical clearance

LC1		D25...D38 (3-pole)
b	without add-on blocks	85
b1	with LAD 4BB	98
with LA4 D●2	114 ⁽¹⁾	
with LA4 DF, DT	123 ⁽¹⁾	
with LA4 DW, DL	130 ⁽¹⁾	
c	without cover or add-on blocks	90
with cover, without add-on blocks	92	
c1	with LAD N or C (2 or 4 contacts)	123
c2	with LA6 DK10, LAD 6K10	135
c3	with LAD T, R, S	143
with LAD T, R, S and sealing cover	147	
(1)	Including LAD 4BB.	

Wiring

