



Osnovne informacije

Grupa proizvoda	TeSys
Ime proizvoda	TeSys LRD TeSys Deca
Tip proizvoda ili komponente	Diferencijalni termički relej preopterećenja
Kratko ime uređaja	LRD
Upotreba releja	Zaštita motora
Kompatibilnost proizvoda	LC1D80 LC1D95
Tip mreže	AC DC
Klasa okidanja preopterećenja	Klasa 10A u skladu sa IEC 60947-4-1
Podešavanje termičkog preopterećenja	23...32 A
[ui] nazivni napon izolacije	Kolo napajanja: 1000 V u skladu sa IEC 60947-4-1 Kolo napajanja: 600 V u skladu sa CSA Kolo napajanja: 600 V u skladu sa UL

Dopunske informacije

Mrežna frekvencija	0...400 Hz
Držač za montažu	Ploča, sa posebnim priborom Šina, sa posebnim priborom Ispod kontaktora
Prag okidanja	1.14 +/- 0.06 Ir u skladu sa IEC 60947-4-1
Sastav pomoćnog kontakta	1 NO + 1 NC
[ith] dozvoljena termička struja u vazduhu	5 A za signalno kolo
Dopustiva struja	0,72 A pri 500 V AC-15 za signalno kolo 0,06 A pri 440 V DC-13 za signalno kolo
[ue] nazivni napon	1000 V AC 0...400 Hz za kolo napajanja u skladu sa IEC 60947-4-1
Pripadajući osigurač	4 A gG for signalno kolo 4 A BS for signalno kolo
[uimp] nazivni podnosivi impulsni napon	6 kV u skladu sa IEC 60947-1
Osetljivost gubitka faze	Struja okidanja 130 % od Ir u dve faze, poslednja na 0
Način upravljanja	Crvena taster: zaustavljanje Plava taster: reset
Temperaturna kompenzacija	-20...60 °C
Povezivanje - priključci	Kolo napajanja: vijčani priključni blokovi 1 kabl(ovi) 4...35 mm ² fleksibilni bez kablovskog završetka Kolo napajanja: vijčani priključni blokovi 1 kabl(ovi) 4...35 mm ² fleksibilni sa kablovskog završetka Kolo napajanja: vijčani priključni blokovi 1 kabl(ovi) 4...35 mm ² jednožični bez kablovskog završetka Upravljačko kolo: vijčani priključni blokovi 2 kabl(ovi) 1...2,5 mm ² fleksibilni bez kablovskog završetka Upravljačko kolo: vijčani priključni blokovi 2 kabl(ovi) 1...2,5 mm ² fleksibilni sa kablovskog završetka Upravljačko kolo: vijčani priključni blokovi 2 kabl(ovi) 1...2,5 mm ² jednožični bez kablovskog završetka
Moment pritezanja	Upravljačko kolo: 1,7 N.m - na vijčani priključni blokovi Kolo napajanja: 9 N.m - na vijčani priključni blokovi
Visina	81 mm
Širina	70 mm
Dubina	115 mm
Masa proizvoda	0,51 kg

Okruženje

Klimatska izdržljivost	U skladu sa IACS E10
Ip stepen zaštite	IP20 conforming to IEC 60529
Temperatura okoline za rad	-20...60 °C bez promene karakteristika u skladu sa IEC 60947-4-1
Temperatura okoline za skladištenje	-60...70 °C
Otpornost na plamen	V1 u skladu sa UL 94
Mehanička robusnost	Vibracije: 6 Gn u skladu sa IEC 60068-2-6 Udara: 15 Gn za 11 ms u skladu sa IEC 60068-2-7
Dielektrična snaga	2,2 kV pri 50 Hz u skladu sa IEC 60947-1
Standardi	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 UL 60947-5-1 CSA C22.2 No 60947-4-1 CSA C22.2 No 60947-5-1 GB/T 14048.4 GB/T 14048.5 EN 50495
Sertifikacija proizvoda	IEC[RETURN]UL[RETURN]CSA[RETURN]CCC[RETURN]EAC[RETURN]ATEX INERIS[RETURN]UKCA

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8,0 cm
Package 1 Width	8,8 cm
Package 1 Length	12,0 cm
Package 1 Weight	498,0 g
Unit Type of Package 2	S02
Number of Units in Package 2	12
Package 2 Height	15,0 cm
Package 2 Width	30,0 cm
Package 2 Length	40,0 cm
Package 2 Weight	6,32 kg
Unit Type of Package 3	P06
Number of Units in Package 3	192
Package 3 Height	77,0 cm
Package 3 Width	80,0 cm
Package 3 Length	60,0 cm
Package 3 Weight	109,62 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACh	 REACh Deklaracija
REACh bez SVHC	Da
EU RoHS direktiva	Usaglašeno  EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	 Informacije O Kraju Radnog Veka

Ugovorna garancija

Garancija	18 meseci
-----------	-----------