



Main

Range	Acti9
Product name	Acti9 xID
Product or component type	Residual current circuit breaker (RCCB)
Device short name	xID
Poles description	2P
Neutral position	Left
[In] rated current	63 A
Network type	AC
Earth-leakage sensitivity	300 mA
Earth-leakage protection time delay	Selective
Earth-leakage protection class	Type A-SI (Super Immunised)
Rated breaking and making capacity	630 A conforming to EN/IEC 61008-1
Suitability for isolation	Yes

Complementary

Network frequency	50 Hz
[Ue] rated operational voltage	230...240 V AC 50 Hz
[Ui] rated insulation voltage	500 V AC 50 Hz
[Uimp] rated impulse withstand voltage	6 kV
Contact position indicator	Yes
Control type	Toggle
Local signalling	ON, OFF, fault trip
Mounting mode	Clip-on
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Downside: biconnect
Connection pitch	18 mm between phases
9 mm pitches	4
Height	81 mm
Width	36 mm
Depth	75 mm
Net weight	210 g
Colour	White
Mechanical durability	4000 cycles
Electrical durability	4000 cycles
Locking options description	Padlocking device
Connections - terminals	Tunnel type terminals (top or bottom) 1...35 mm ² rigid Tunnel type terminals (top or bottom) 1...25 mm ² flexible
Wire stripping length	14 mm for top or bottom connection
Tightening torque	3.5 N.m top or bottom

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Standards	IEC 61008-2-1 EN 61008-2-1 EN/IEC 61008-1
Product certifications	ISI
IP degree of protection	IP20
Pollution degree	2
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.2 cm
Package 1 Width	3.8 cm
Package 1 Length	8.4 cm
Package 1 Weight	0.18 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	10 cm
Package 2 Width	9.5 cm
Package 2 Length	26 cm
Package 2 Weight	1.32 kg
Unit Type of Package 3	S03
Number of Units in Package 3	54
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	12.367 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------