



Osnovne informacije

Grupa proizvoda	TeSys TeSys Deca
Ime proizvoda	TeSys LRD TeSys Deca
Tip proizvoda ili komponente	Diferencijalni termički relej preopterećenja
Kratko ime uređaja	LRD
Upotreba releja	Zaštita motora
Kompatibilnost proizvoda	LC1D65A LC1D50A
Tip mreže	DC AC
Klasa okidanja preopterećenja	Klasa 10A u skladu sa IEC 60947-4-1
Podešavanje termičkog preopterećenja	48...65 A
[ui] nazivni napon izolacije	Kolo napajanja: 600 V u skladu sa CSA Kolo napajanja: 600 V u skladu sa UL Kolo napajanja: 690 V u skladu sa IEC 60947-4-1

Dopunske informacije

Mrežna frekvencija	0...400 Hz
Držač za montažu	Ploča, sa posebnim priborom Šina, sa posebnim priborom Ispod kontaktora
Prag okidanja	1.14 +/- 0.06 Ir u skladu sa IEC 60947-4-1
Sastav pomoćnog kontakta	1 NO + 1 NC
[ith] dozvoljena termička struja u vazduhu	5 A za signalno kolo
Dopustiva struja	0,95 A pri 380 V AC-15 za signalno kolo 0,06 A pri 440 V DC-13 za signalno kolo
[ue] nazivni napon	690 V AC 0...400 Hz za kolo napajanja u skladu sa IEC 60947-4-1
Pripadajući osigurač	4 A gG for signalno kolo 4 A BS for signalno kolo
[uimp] nazivni podnosivi impulsni napon	6 kV
Osetljivost gubitka faze	Struja okidanja 130 % od Ir u dve faze, poslednja na 0
Način upravljanja	Crvena taster: zaustavljanje Plava taster: reset
Temperaturna kompenzacija	-20...60 °C
Povezivanje - priključci	Upravljačko kolo: vijčani priključni blokovi 2 kabl(ovi) 1...2,5 mm ² fleksibilni bez kablovskog završetka Upravljačko kolo: vijčani priključni blokovi 2 kabl(ovi) 1...2,5 mm ² fleksibilni sa kablovskog završetka Upravljačko kolo: vijčani priključni blokovi 2 kabl(ovi) 1...2,5 mm ² jednožični bez kablovskog završetka Kolo napajanja: EverLink BTR vijčani priključak 1 kabl(ovi) 1...35 mm ² fleksibilni bez kablovskog završetka Kolo napajanja: EverLink BTR vijčani priključak 1 kabl(ovi) 1...35 mm ² fleksibilni sa kablovskog završetka Kolo napajanja: EverLink BTR vijčani priključak 1 kabl(ovi) 1...35 mm ² jednožični bez kablovskog završetka
Moment pritezanja	Upravljačko kolo: 1,7 N.m - na vijčani priključni blokovi Kolo napajanja: 5 N.m - na EverLink BTR vijčani priključak
Visina	70 mm
Širina	55 mm

Dubina	123 mm
Masa proizvoda	0,375 kg

Okruženje

Klimatska izdržljivost	U skladu sa IACS E10
Ip stepen zaštite	IP20 conforming to IEC 60529
Temperatura okoline za rad	-20...60 °C bez promene karakteristika u skladu sa IEC 60947-4-1
Temperatura okoline za skladištenje	-60...70 °C
Otpornost na plamen	V1 u skladu sa UL 94
Mehanička robusnost	Udara: 15 Gn za 11 ms u skladu sa IEC 60068-2-7 Vibracije: 4 gn u skladu sa IEC 60068-2-6
Dielektrična snaga	1,89 kV pri 50 Hz u skladu sa IEC 60947-1
Standardi	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 UL 60947-5-1 CSA C22.2 No 60947-4-1 CSA C22.2 No 60947-5-1 GB/T 14048.4 GB/T 14048.5 EN 50495
Sertifikacija proizvoda	IEC[RETURN]UL[RETURN]CSA[RETURN]CCC[RETURN]EAC[RETURN]DNV-GL[RETURN]RMRS[RETURN]EU-RO MR[RETURN]LROS (Lloyds register of shipping)[RETURN]ATEX INERIS[RETURN]UKCA

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6,200 cm
Package 1 Width	11,000 cm
Package 1 Length	14,000 cm
Package 1 Weight	394,000 g
Unit Type of Package 2	S02
Number of Units in Package 2	13
Package 2 Height	15,000 cm
Package 2 Width	30,000 cm
Package 2 Length	40,000 cm
Package 2 Weight	5,453 kg
Unit Type of Package 3	P06
Number of Units in Package 3	208
Package 3 Height	75,000 cm
Package 3 Width	60,000 cm
Package 3 Length	80,000 cm
Package 3 Weight	97,732 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACh	 REACh Deklaracija
REACh bez SVHC	Da
EU RoHS direktiva	Usaglašeno  EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	 Informacije O Kraju Radnog Veka

Ugovorna garancija

Garancija	18 meseci
-----------	-----------