



Osnovne informacije

Grupa proizvoda	EasyPact
Grupa proizvoda	Easypact CVS100...250
Ime proizvoda	EasyPact CVS
Kratko ime uređaja	CVS250B
Tip proizvoda ili komponente	Prekidač
Primena uređaja	Razvod električne energije
Broj polova	3P
Opis zaštićenih polova	3d
Zaštita od struje curenja (dodatak Vigi)	Bez
[In] nazivna struja	250 A pri 40 °C
Tip mreže	AC
Kategorija upotrebe	Kategorija A
[Icu] prekidna moć	40 kA Icu pri 220/240 V AC 50/60 Hz u skladu sa IEC 60947-2 25 kA Icu pri 380/415 V AC 50/60 Hz u skladu sa IEC 60947-2 20 kA Icu pri 440 V AC 50/60 Hz u skladu sa IEC 60947-2
Ime zaštitne jedinice	TM-D
Tehnologija zaštitne jedinice	Termomagnetna
Veličina zaštitne jedinice	250 A pri 40 °C
Tip zaštite	Zaštita od kratkog spoja Zaštita od preopterećenja (termičkog)

Dopunske informacije

[uimp] nazivni podnosivi impulsni napon	8 kV conforming to EN/IEC 60947-2
Mrežna frekvencija	50/60 Hz
Kod prekidne moći	B
[Ics] servisna prekidna moć	15 kA pri 440 V AC 50/60 Hz u skladu sa IEC 60947-2 25 kA pri 380/415 V AC 50/60 Hz u skladu sa IEC 60947-2 40 kA pri 220/240 V AC 50/60 Hz u skladu sa IEC 60947-2
Mehanička trajnost	20000 ciklusa
Električna trajnost	10000 ciklusa 415 V In u skladu sa IEC 60947-2
Tip upravljanja	Ručica
Podešavanje termičkog preopterećenja	175...250 A
Podešavanje praga zaštite od preopterećenja Ir	Podesivo
Podešavanje gornjeg praga prorade zaštite od preopterećenja	0.7...1 x In
Tip podešavanja kašnjenja prorade zaštite	Fiksno
Podešavanje praga trenutne zaštite od kratkog spoja tip II	Fiksno
Podešavanje praga trenutne zaštite od kratkog spoja	2500 A
Indikator pozicije kontakta	Da
Nosači za montažu	Zadnja ploča
Način montiranja	Fiksno
Gornji priključak	Prednja

Donji priključak	Prednji
Povezivanje - priključci	Priključak na zavrtanj
Povezivanje	35 mm
Kompatibilnost	CVS250
Širina	105 mm
Dubina	86 mm
Visina	161 mm
Masa proizvoda	1,7 kg

Okruženje

Standardi	IEC 60947-2 EN 60947-2
Sertifikacija proizvoda	IEC[RETURN]GOST
Klasa zaštite od električnog udara	Klasa II
Stepen zaprljanosti	3 u skladu sa IEC 60664-1
Ip stepen zaštite	IP40
Temperatura okoline za rad uređaja	-25...70 °C
Temperatura okoline za skladištenje	-50...85 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11,000 cm
Package 1 Width	14,000 cm
Package 1 Length	19,000 cm
Package 1 Weight	1,935 kg
Unit Type of Package 2	S03
Number of Units in Package 2	8
Package 2 Height	30,000 cm
Package 2 Width	30,000 cm
Package 2 Length	40,000 cm
Package 2 Weight	15,903 kg
Unit Type of Package 3	P12
Number of Units in Package 3	64
Package 3 Height	45,000 cm
Package 3 Width	80,000 cm
Package 3 Length	120,000 cm
Package 3 Weight	139,226 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACh	 REACH Deklaracija
EU RoHS direktiva	У складу са изузецима
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	 Informacije O Kraju Radnog Veka
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.