



Osnovne informacije

Grupa proizvoda	Harmony Control Relays
Tip releja	Kontrolni relej
Tip proizvoda ili komponente	3-phase control relay
Specifične primene proizvoda	Za trofazno napajanje
Ime releja	RM17TG
Nadzirani parametri releja	Redosled faza Detekcija otkaza faze (2 ili više faza)
Vremensko kašnjenje	Bez
Preklopna moć u va	1250 VA
Opseg merenja	208...480 V AC
Tip kontakata i sastav	2 C/O
[uc] napon upravljačkog kola	208...440 V

Dopunske informacije

Maksimalni napon preklapanja	250 V AC 250 V DC
Minimalna struja preklapanja	10 mA pri 5 V DC
[Un] rated nominal voltage	, self-powered
Granice napona	183...484 V AC
Ograničenje napona upravljačkog kola	- 12 % + 10 % Un
Snaga potrošnje u va	0...22 VA pri 400 V AC 50 Hz
Prag detekcije napona	< 100 V AC
Frekvencija upravljačkog kola	50...60 Hz +/- 10 %
Izlazni kontakti	2 C/O
Nazivna izlazna struja	5 A
Granice merenog napona	183...484 V AC
Kašnjenje pri uključivanju	650 milisekundi
Opseg napona	183...484 V
Vreme odziva	<= 130 ms (u slučaju greške)
Označavanje	CE
Kategorija prenapona	III u skladu sa IEC 60664-1
Otpornost izolacije	> 500 MOhm pri 500 V DC u skladu sa IEC 60255-5 > 500 MOhm pri 500 V DC u skladu sa IEC 60664-1
[ui] nazivni napon izolacije	400 V u skladu sa IEC 60664-1
Frekvencija napajanja	50/60 Hz +/- 10 %
Radni položaj	Bilo koja pozicija bez smanjenja karakteristika
Povezivanje - priključci	Vijčani priključci, 1 x 0.5...1 x 4 mm ² (AWG 20...AWG 11) jednožični bez kablovskog završetka Vijčani priključci, 2 x 0.5...2 x 2.5 mm ² (AWG 20...AWG 14) jednožični bez kablovskog završetka Vijčani priključci, 1 x 0.2...1 x 2.5 mm ² (AWG 24...AWG 12) fleksibilni sa kablovskim završetkom Vijčani priključci, 2 x 0.2...2 x 1.5 mm ² (AWG 24...AWG 16) fleksibilni sa kablovskim završetkom
Moment pritezanja	0,6...1 N.m u skladu sa IEC 60947-1
Materijal kućišta	Samogasiva plastika

Informacije navedene u ovoj dokumentaciji predstavljaju opšti opis odnosno tehničke karakteristike performansi proizvoda. Dokumentacija nije namenjena da bude zamena za niti se može koristiti za određivanje prikladnosti i pouzdanosti proizvoda za specifičnu krajnju primenu. Dužnost je korisnika odnosno integratora da izvrši primerenu i sveobuhvatnu analizu rizika, procenu i proveru proizvoda u pogledu odgovarajuće specifične primene ili načina korišćenja. Ni Schneider Electric Industries SAS ni njegova društva ili zavisna društva neće snositi odgovornost za zloupotrebu ovde navedenih informacija.

Lokalna signalizacija	Zarelej ON: LED (žuta)
Držač za montažu	35 mm simetrična DIN šina u skladu sa IEC 60715
Električna trajnost	10000 ciklusa
Mehanička trajnost	30000000 ciklusa
Broj operacija	<= 360 operacija/h punog opterećenja
Kategorija upotrebe	AC-12 u skladu sa IEC 60947-5-1 AC-13 u skladu sa IEC 60947-5-1 AC-14 u skladu sa IEC 60947-5-1 AC-15 u skladu sa IEC 60947-5-1 DC-12 u skladu sa IEC 60947-5-1 DC-13 u skladu sa IEC 60947-5-1
Sigurnosni podaci o pouzdanosti	B10d = 850000 MTTFd = 924.6 godina
Širina	17,5 mm
Masa proizvoda	0,13 kg
Tip upravljanja	Bez test tastera

Okruženje

Elektromagnetna kompatibilnost	Standard emisije za industrijske sredine conforming to IEC 61000-6-4 Standard emisije za stambene, poslovne i lake industrijske sredine conforming to IEC 61000-6-3 Otpornost za industrijske sredine conforming to IEC 61000-6-2
Standardi	IEC 60255-1
Sertifikacija proizvoda	GOST[RETURN]C-Tick[RETURN]UL[RETURN]CSA[RETURN]GL
Direktive	73/23/EEC -niskonaponska direktiva 89/336/EEC - elektromagnetna kompatibilnost
Temperatura okoline za skladištenje	-40...70 °C
Temperatura okoline za rad	-20...50 °C
Relativna vlažnost	95 % pri 55 °C u skladu sa IEC 60068-2-30
Otpornost na vibracije	0.35 mm (f= 5...57,6 Hz) u skladu sa IEC 60068-2-6 1 gn (f= 57,6...150 Hz) u skladu sa IEC 60255-21-1
Otpornost na udare	15 gn za 11 milisekundi u skladu sa IEC 60255-21-1
Ip stepen zaštite	IP20 u skladu sa IEC 60529 (priključci) IP30 u skladu sa IEC 60529 (kućište)
Stepen zaprljanosti	3 u skladu sa IEC 60664-1
Dielektrični test napon	2 kV AC 50 Hz, 1 min
Nerasut udarni talas	4 kV

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2,700 cm
Package 1 Width	7,800 cm
Package 1 Length	9,700 cm
Package 1 Weight	98,000 g
Unit Type of Package 2	S02
Number of Units in Package 2	48
Package 2 Height	15,000 cm
Package 2 Width	30,000 cm
Package 2 Length	40,000 cm
Package 2 Weight	5,150 kg
Unit Type of Package 3	P06
Number of Units in Package 3	768
Package 3 Height	75,000 cm
Package 3 Width	60,000 cm
Package 3 Length	80,000 cm
Package 3 Weight	87,204 kg

Održivost ponude


Status održive ponude	Green Premium proizvod
Propis REACh	 REACh Deklaracija
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	 Informacije O Kraju Radnog Veka

Ugovorna garancija

Garancija	18 meseci
-----------	-----------


3-Phase Supply Control Relays

Dimensions and Mounting




3-Phase Supply Control Relays

Wiring Diagram



Application Scheme


Example



(1) Fault

Function Diagram

Phase Sequence Control and Total Loss of Phase Detection



Legend

Tr Response time on appearance of a fault
L1, L2, L3 Phases of the supply voltage monitored
R - R1/R2 Output relay(s),
Relay status: black color = energized.