

BSH1004P11A2A

servo motor BSH, Lexium 05, 9.31N.m,
1500rpm, 100mm, keyed shaft, Sincos single
turn, without brake, IP50





Main

Product or component type	Servo motor
Device short name	B5H
Maximum mechanical speed	6000 rpm
Continuous stall torque	<p>8 N.M for LXM32.D30N4 at 10 A, 400 V, three phase</p> <p>8 N.M for LXM32.D30N4 at 10 A, 480 V, three phase</p> <p>9.31 N.M for LXM15MD40N4, 400 V, three phase</p> <p>9.31 N.M for LXM15MD40N4, 480 V, three phase</p> <p>9.31 N.M for LXM15MD28M3, 230 V, three phase</p> <p>9.31 N.M for LXM15MD28N4, 230 V, three phase</p> <p>9.31 N.M for LXM15MD28N4, 400 V, three phase</p> <p>9.31 N.M for LXM15MD28N4, 480 V, three phase</p> <p>9.31 N.M for LXM15MD40N4, 230 V, three phase</p> <p>9.31 N.M for LXM15MD40N4, 480 V, three phase</p> <p>9.31 N.M for LXM05AD34N4, 380...480 V, three phase</p> <p>9.31 N.M for LXM05AD42M3X, 200...240 V, three phase</p> <p>9.31 N.M for LXM05AD57N4, 380...480 V, three phase</p> <p>9.31 N.M for LXM05BD34N4, 380...480 V, three phase</p> <p>9.31 N.M for LXM05BD42M3X, 200...240 V, three phase</p> <p>9.31 N.M for LXM05BD57N4, 380...480 V, three phase</p> <p>9.31 N.M for LXM05CD34N4, 380...480 V, three phase</p> <p>9.31 N.M for LXM05CD42M3X, 200...240 V, three phase</p> <p>9.31 N.m for LXM05CD57N4, 380...480 V, three phase</p>
Peak stall torque	<p>37.9 N.M for LXM32.D30N4 at 10 A, 400 V, three phase</p> <p>37.9 N.M for LXM32.D30N4 at 10 A, 480 V, three phase</p> <p>25.7 N.M for LXM15MD28M3, 230 V, three phase</p> <p>25.7 N.M for LXM15MD28N4, 230 V, three phase</p> <p>25.7 N.M for LXM15MD28N4, 400 V, three phase</p> <p>25.7 N.M for LXM15MD28N4, 480 V, three phase</p> <p>33.83 N.M for LXM15MD40N4, 230 V, three phase</p> <p>33.83 N.M for LXM15MD40N4, 400 V, three phase</p> <p>33.83 N.M for LXM15MD40N4, 480 V, three phase</p> <p>23.47 N.M for LXM05AD34N4, 380...480 V, three phase</p> <p>35.7 N.M for LXM05AD42M3X, 200...240 V, three phase</p> <p>35.7 N.M for LXM05AD57N4, 380...480 V, three phase</p> <p>23.47 N.M for LXM05BD34N4, 380...480 V, three phase</p> <p>35.7 N.M for LXM05BD42M3X, 200...240 V, three phase</p> <p>35.7 N.M for LXM05BD57N4, 380...480 V, three phase</p> <p>23.47 N.M for LXM05CD34N4, 380...480 V, three phase</p> <p>35.7 N.M for LXM05CD42M3X, 200...240 V, three phase</p> <p>35.7 N.m for LXM05CD57N4, 380...480 V, three phase</p>

Nominal output power	<p>2600 W for LXM32.D30N4 at 10 A, 480 V, three phase</p> <p>2100 W for LXM32.D30N4 at 10 A, 400 V, three phase</p> <p>1300 W for LXM05AD42M3X, 200...240 V, three phase</p> <p>1300 W for LXM05BD42M3X, 200...240 V, three phase</p> <p>1300 W for LXM05CD42M3X, 200...240 V, three phase</p> <p>1300 W for LXM15MD28M3, 230 V, three phase</p> <p>1300 W for LXM15MD28N4, 230 V, three phase</p> <p>1300 W for LXM15MD40N4, 230 V, three phase</p> <p>2200 W for LXM05AD34N4, 380...480 V, three phase</p> <p>2200 W for LXM05AD57N4, 380...480 V, three phase</p> <p>2200 W for LXM05BD34N4, 380...480 V, three phase</p> <p>2200 W for LXM05BD57N4, 380...480 V, three phase</p> <p>2200 W for LXM05CD34N4, 380...480 V, three phase</p> <p>2200 W for LXM05CD57N4, 380...480 V, three phase</p> <p>2200 W for LXM15MD28N4, 400 V, three phase</p> <p>2300 W for LXM15MD40N4, 400 V, three phase</p> <p>2400 W for LXM15MD40N4, 480 V, three phase</p> <p>2700 W for LXM15MD28N4, 480 V, three phase</p>
Nominal torque	<p>8.3 N.M for LXM32.D30N4 at 10 A, 400 V, three phase</p> <p>8.3 N.M for LXM32.D30N4 at 10 A, 480 V, three phase</p> <p>6.5 N.M for LXM15MD28N4, 480 V, three phase</p> <p>6.69 N.M for LXM15MD40N4, 480 V, three phase</p> <p>7 N.M for LXM15MD28N4, 400 V, three phase</p> <p>7.1 N.M for LXM05AD34N4, 380...480 V, three phase</p> <p>7.1 N.M for LXM05AD57N4, 380...480 V, three phase</p> <p>7.1 N.M for LXM05BD34N4, 380...480 V, three phase</p> <p>7.1 N.M for LXM05BD57N4, 380...480 V, three phase</p> <p>7.1 N.M for LXM05CD34N4, 380...480 V, three phase</p> <p>7.1 N.M for LXM05CD57N4, 380...480 V, three phase</p> <p>7.17 N.M for LXM15MD40N4, 400 V, three phase</p> <p>8.18 N.M for LXM15MD40N4, 230 V, three phase</p> <p>8.22 N.M for LXM05AD42M3X, 200...240 V, three phase</p> <p>8.22 N.M for LXM05BD42M3X, 200...240 V, three phase</p> <p>8.22 N.M for LXM05CD42M3X, 200...240 V, three phase</p> <p>8.22 N.M for LXM15LD28M3, 230 V, three phase</p> <p>8.22 N.m for LXM15MD28N4, 230 V, three phase</p>

Nominal speed	2500 rpm for LXM32.D30N4 at 10 A, 400 V, three phase 3000 rpm for LXM32.D30N4 at 10 A, 480 V, three phase 1500 rpm for LXM05AD42M3X, 200...240 V, three phase 1500 rpm for LXM05BD42M3X, 200...240 V, three phase 1500 rpm for LXM05CD42M3X, 200...240 V, three phase 3000 rpm for LXM05AD34N4, 380...480 V, three phase 3000 rpm for LXM05BD34N4, 380...480 V, three phase 3000 rpm for LXM05CD34N4, 380...480 V, three phase 1500 rpm for LXM15MD28M3, 230 V, three phase 1500 rpm for LXM15MD28N4, 230 V, three phase 1500 rpm for LXM15MD40N4, 230 V, three phase 3000 rpm for LXM05AD57N4, 380...480 V, three phase 3000 rpm for LXM05BD57N4, 380...480 V, three phase 3000 rpm for LXM05CD57N4, 380...480 V, three phase 3000 rpm for LXM15MD28N4, 400 V, three phase 3000 rpm for LXM15MD40N4, 400 V, three phase 3500 rpm for LXM15MD40N4, 480 V, three phase 4000 rpm for LXM15MD28N4, 480 V, three phase
Product compatibility	LXM05AD42M3X at 200...240 V three phase LXM05BD42M3X at 200...240 V three phase LXM05CD42M3X at 200...240 V three phase LXM05AD34N4 at 380...480 V three phase LXM05BD34N4 at 380...480 V three phase LXM05CD34N4 at 380...480 V three phase LXM15MD28N4 at 400 V three phase LXM15MD28N4 at 480 V three phase LXM15MD40N4 at 400 V three phase LXM15MD40N4 at 480 V three phase LXM32.D30N4 at 400 V three phase LXM32.D30N4 at 480 V three phase LXM05AD57N4 at 380...480 V three phase LXM05BD57N4 at 380...480 V three phase LXM05CD57N4 at 380...480 V three phase LXM15MD28M3 at 230 V three phase LXM15MD28N4 at 230 V three phase LXM15MD40N4 at 230 V three phase
Shaft end	Keyed
IP degree of protection	IP50 standard
Speed feedback resolution	131072 points/turn
Holding brake	Without
Mounting support	International standard flange
Electrical connection	Rotatable right-angled connectors

Complementary

Range compatibility	Lexium 15 Lexium 32 Lexium 05
Supply voltage max	480 V
Network number of phases	Three phase
Continuous stall current	6.2 A
Maximum continuous power	3.64 W

Maximum current Irms	34.8 A for LXM15LD28M3 34.8 A for LXM15MD28N4 34.8 A for LXM15MD40N4 32.3 A for LXM05AD42M3X 32.3 A for LXM05AD34N4 32.3 A for LXM05AD57N4 32.3 A for LXM05BD42M3X 32.3 A for LXM05BD34N4 32.3 A for LXM05BD57N4 32.3 A for LXM05CD42M3X 32.3 A for LXM05CD34N4 32.3 A for LXM05CD57N4 30 A for LXM32.D30N4
Maximum permanent current	32.3 A
Switching frequency	8 kHz
Second shaft	Without second shaft end
Shaft diameter	24 mm
Shaft length	50 mm
Key width	40 mm
Feedback type	Single turn SinCos Hiperface
Motor flange size	100 mm
Number of motor stacks	4
Torque constant	1.62 N.m/A at 120 °C
Back emf constant	103 V/krpm at 120 °C
Number of motor poles	8
Rotor inertia	4.22 kg.cm ²
Stator resistance	1.81 Ohm at 20 °C
Stator inductance	11.8 mH at 20 °C
Stator electrical time constant	6.52 ms at 20 °C
Maximum radial force Fr	1070 N at 1000 rpm 740 N at 3000 rpm 850 N at 2000 rpm
Maximum axial force Fa	0.2 x Fr
Type of cooling	Natural convection
Length	276.5 mm
Centring collar diameter	95 mm
Centring collar depth	3.5 mm
Number of mounting holes	4
Mounting holes diameter	9 mm
Circle diameter of the mounting holes	115 mm
Net weight	9.5 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	20.000 cm
Package 1 Width	26.000 cm
Package 1 Length	60.000 cm
Package 1 Weight	10.571 kg
Unit Type of Package 2	P06
Number of Units in Package 2	8
Package 2 Height	75.000 cm
Package 2 Width	80.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	90.500 kg

Offer Sustainability


Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Servo Motors Dimensions

Example with Straight Connectors



- a: Power supply for servo motor brake
- b: Power supply for servo motor encoder
- (1) M4 screw
- (2) Shaft end, keyed slot (optional)

Dimensions in mm

Straight connectors		Rotatable angled connectors		c (without brake)	c (with brake)	c1	c2	h	h1	Ø	Ø1 for screws
b1	b2	b1	b2								
39.5	25.5	39.5	39.5	277	308	50	40	8 N9	4 ^{+0.1} ₀	24 k6	M8 x 19


Dimensions in in.

Straight connectors		Rotatable angled connectors		c (without brake)	c (with brake)	c1	c2	h	h1	Ø	Ø1 for screws
b1	b2	b1	b2								
1.55	1.00	1.55	1.55	10.90	12.12	1.96	1.57	0.31 N9	0.16 ^{+0.1} ₀	0.94 k6	M8 x 0.75

400 V 3-Phase Supply Voltage

Torque/Speed Curves

Servo motor with LXM32-D30N4 servo drive



X Speed in rpm

Y Torque in Nm


1 Peak torque

2 Continuous torque

480 V 3-Phase Supply Voltage

Torque/Speed Curves

Servo motor with LXM32-D30N4 servo drive



X Speed in rpm

Y Torque in Nm

1 Peak torque

2 Continuous torque