



Osnovne informacije

Grupa proizvoda	Harmony XVB Universal
Tip proizvoda ili komponente	Osnovna jedinica
Ime komponente	XVBC
Materijal	Staklo ojačano poliamidom: bazi

Dopunske informacije

Način pričvršćivanja	Direktnom ili montažom na cev
Prečnik za montiranje	70 mm
Namena proizvoda	Blok bez jedinice za snažan bljesak
Električna veza	1 konektor za standardni ulaz
Kablovski uvod	Uvod na donjoj ili bočnoj strani
Način spajanja	Za sastavljanje kod korisnika, do 5 jedinica
Opis priključaka iso n°1	(COM-2)PW (COM-3)PW (COM-1)PW (GND)GROUND (COM-4)PW (COM-5)PW
Masa proizvoda	0,16 kg

Okruženje

Sertifikacija proizvoda	CCC[RETURN]EAC[RETURN]CSA C22-2 No 14[RETURN]UL 508
Standardi	EN/IEC 60947-5-1
Tretman zaštite	TC
Temperatura okoline za skladištenje	-40...70 °C
Nema stepen zaštite	Type 4X u skladu sa UL (u zatvorenom)

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10 cm
Package 1 Width	12 cm
Package 1 Length	10 cm
Package 1 Weight	170 g
Unit Type of Package 2	S03
Number of Units in Package 2	36
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	7 kg
Unit Type of Package 3	P06

Number of Units in Package 3	144
Package 3 Height	45 cm
Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	36,5 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACh	 REACh Deklaracija
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.


Ugovorna garancija

Garancija	18 meseci
-----------	-----------

Indicator Bank with “Flash” Discharge Tube Unit

Dimensions

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get b dimension.




- (1) Base unit
- (2) Illuminated or audible signalling unit XVBC•••, to be ordered separately
- (3) “Flash” unit XVBC•••, to be ordered separately

Number of illuminated or audible signalling units other than “flash” tube	b in mm	b in in.
1	295	11.61
2	358	14.09
3	421	16.57
4	484	19.06

Base Unit for Indicator Banks

Panel Cut-out for Direct Fixing



Illuminated Beacon

Wiring Diagram

