



Main

Range	Easy TeSys
Range of product	Easy TeSys Control
Product or component type	Contactor
Device short name	LC1E
Contactor application	Resistive load Motor control
Utilisation category	AC-1 AC-3
Poles description	3P
[Ue] rated operational voltage	Power circuit: ≤ 690 V AC 50/60 Hz
[Ie] rated operational current	200 A (at ≤55 °C) at ≤ 440 V AC AC-3 for power circuit 250 A (at ≤40 °C) at ≤ 440 V AC AC-1 for power circuit
[Uc] control circuit voltage	220 V AC 50 Hz

Complementary

Motor power kW	55 kW at 220...230 V AC 50/60 Hz 90 kW at 380...400 V 100 kW at 415 V 100 kW at 440 V 110 kW at 500 V 110 kW at 660...690 V
Pole contact composition	3 NO
[Ith] conventional free air thermal current	250 A (at 55 °C)
Irms rated making capacity	2000 A at 440 V AC for power circuit conforming to IEC 60947-4-1
Rated breaking capacity	1600 A at 440 V for power circuit conforming to IEC 60947
[Icw] rated short-time withstand current	1500 A 40 °C - 10 s for power circuit
Associated fuse rating	10 A gG at ≤ 690 V coordination type 1 for control circuit conforming to IEC 60947-5-1 315 A gG at ≤ 690 V coordination type 1 for power circuit
Average impedance	0.33 mOhm - Ith 250 A 50 Hz for power circuit
Power dissipation per pole	13 W AC-3 21 W AC-1
[Ui] rated insulation voltage	690 V conforming to IEC 60947-4-1
Overvoltage category	III
Pollution degree	3
[Uimp] rated impulse withstand voltage	8 kV coil not connected to the power circuit conforming to IEC 60947
Mechanical durability	5000000 cycles
Electrical durability	500000 Cycles AC-3 200000 cycles AC-1
Control circuit type	AC at 50 Hz
Control circuit voltage limits	0.85...1.1 Uc (-5...55 °C):operational 50 Hz 0.35...0.55 Uc (-5...55 °C):drop-out 50 Hz
Inrush power in VA	805 VA 50 Hz cos phi 0.3 (at 20 °C) 970 VA 60 Hz cos phi 0.3 (at 20 °C)
Hold-in power consumption in VA	55 VA 50 Hz cos phi 0.3 (at 20 °C) 66 VA 60 Hz cos phi 0.3 (at 20 °C)
Heat dissipation	18...24 W for control circuit

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company Schneider Electric. This information is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Operating time	20...35 ms on closing 7...15 ms on opening
Maximum operating rate	1200 cyc/h 55 °C
Connections - terminals	Control circuit: screw clamp terminals 1 1...4 mm ² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 1...4 mm ² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 1...2.5 mm ² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 1...4 mm ² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 1...4 mm ² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 1 1...2.5 mm ² - cable stiffness: flexible with cable end Power circuit: cable with lug - external diameter: 150 mm Power circuit: bars 2 - busbar cross section: 3 x 25 mm
Tightening torque	Control circuit: 1.2 N.m Power circuit: 18 N.m
Minimum switching voltage	17 V for control circuit
Minimum switching current	5 mA for control circuit
Insulation resistance	> 10 MOhm for control circuit
Non-overlap time	1.5 Ms on energisation guaranteed between NC and NO contact 1.5 ms on de-energisation guaranteed between NC and NO contact
Mounting support	Plate

Environment

Standards	IEC 60947-1 IEC 60947-4-1 IEC 60947-5-1
Product certifications	EAC[RETURN]CE
IP degree of protection	IP2X conforming to IEC 60529
Protective treatment	TH (pollution degree 3) conforming to IEC 60068-2-30 test Db
Permissible ambient air temperature around the device	-20...70 °C at Uc -60...80 °C storage -5...55 °C operation
Operating altitude	3000 m without derating
Fire resistance	850 °C conforming to IEC 60695-2-1
Mechanical robustness	Vibrations contactor open (1.5 Gn, 5...300 Hz) Vibrations contactor closed (3 Gn, 5...300 Hz) Shocks contactor open (6 Gn for 11 ms) Shocks contactor closed (7 Gn for 11 ms)
Height	174 mm
Width	168.5 mm
Depth	181 mm
Net weight	4.6 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	24.5 cm
Package 1 Width	23.5 cm
Package 1 Length	25.0 cm
Package 1 Weight	5.097 kg
Unit Type of Package 2	P06
Number of Units in Package 2	12
Package 2 Height	80.0 cm
Package 2 Width	80.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	75.22 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------