

# Tehničke karakteristike proizvoda

## Karakteristike

# MUR36024

Mureva Styl - utičnica + naizmjenični prekidač - siva



### Osnovne informacije

Grupa proizvoda	Mureva Styl
Tip proizvoda ili komponente	Prekidač i utičnica
Prezentacija uređaja	Kompletan proizvod
Nijansa boje	Siva (RAL 7016)

### Dopunske informacije

Montaža uređaja	Nadgradno
Materijal	PC (polikarbonat) Mesing
Vrsta tehnologije	Elektromehanička
Broj prekidača	1
Funkcija prekidača	Jednopolni naizmjenični
Konfiguracija polova utičnice	2P + E
Opis standarda utičnice	Uzemljenje sa strane
Outlet standard deviation	Šuko
Pravac instalacije	Vertikalno
[ue] nazivni napon	250 V
Tip mreže	AC
Mrežna frekvencija	50/60 Hz
Nazivna struja	10 AX
Visina	147 mm
Širina	76 mm
Dubina	64 mm
Chemical and detergent products resistance	Otporan na alkohol (70%) Otporan na alkohol (96%) Otporan na A-mlečnu kiselinu Otporan na razblaženi kvarterni amonijum Otporan na razblaženo izbeljivač Otporan na razblažen amonijak Otporan na vodu sa sapunom Otporan na čistač kristala Otporan na vodonik peroksid 10 zapremina Otporan na heksan

### Okruženje

Oznake kvaliteta	EAC CE AENOR
Ip stepen zaštite	IP55
Ik stepen zaštite	IK08

## Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6,500 cm
Package 1 Width	7,500 cm
Package 1 Length	14,500 cm
Package 1 Weight	232,300 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	8,000 cm
Package 2 Width	16,000 cm
Package 2 Length	39,500 cm
Package 2 Weight	1,266 kg
Unit Type of Package 3	S04
Number of Units in Package 3	30
Package 3 Height	30,000 cm
Package 3 Width	40,000 cm
Package 3 Length	60,000 cm
Package 3 Weight	8,251 kg

## Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	<a href="#">REACH Deklaracija</a>
EU RoHS direktiva	Usaglašeno <a href="#">EU RoHS Deklaracija</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
RoHS regulativa za Kinu	<a href="#">RoHS Deklaracija Za Kinu</a>
Izjava o zaštiti životne sredine	<a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja