



## Main

Device short name	MT400/630
Product or component type	Motor mechanism
Device application	Automatic spring charging
Range compatibility	ComPact NSX400 ComPact NSX630 Compact NSX400 DC Compact NSX630 DC PowerPact Multistandard EasyPact CVS400 EasyPact CVS630 PowerPact L
Control type	Standard
[Uc] control circuit voltage	208...277 V AC 60 Hz 220...240 V AC 50/60 Hz
Circuit breaker mounting mode	Fixed
Circuit breaker frame rated current	400 A 630 A

## Complementary

Control signal type	Impulse Maintained
Response time	< 700 ms (opening) < 80 ms (closing)
Maximum operating frequency	4 per minute
Maximum power consumption in VA	500 VA closing 500 VA opening
Locking options description	Padlocking in OFF position 1 to 3 padlocks Ø 5 to Ø 8

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	3.15 kg
Package 1 Height	19.8 cm
Package 1 width	17.5 cm
Package 1 Length	17.5 cm
Unit Type of Package 2	S04
Number of Units in Package 2	6
Package 2 Weight	19.654 kg
Package 2 Height	30 cm
Package 2 width	40 cm
Package 2 Length	60 cm
Unit Type of Package 3	P12
Number of Units in Package 3	24
Package 3 Weight	90.616 kg
Package 3 Height	50 cm

Package 3 width	80 cm
Package 3 Length	120 cm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

### Contractual warranty

Warranty	18 months
----------	-----------