



Main

Device short name	MT400/630
Product or component type	Motor mechanism
Device application	Automatic spring charging
Range compatibility	ComPacT new generation (ComPacT NSX400 new generation) ComPacT new generation (ComPacT NSX630 new generation) ComPact (ComPact NSX400) ComPact (ComPact NSX630) ComPact (ComPacT NSX DC new generation) NSX400 DC ComPact (ComPacT NSX DC new generation) NSX630 DC ComPact Compact NSX400 DC ComPact Compact NSX630 DC PowerPact Multistandard (PowerPact Multistandard) EasyPact (EasyPact CVS400) EasyPact (EasyPact CVS630) PowerPact (PowerPact L)
Control type	Standard
[Uc] control circuit voltage	110...130 V DC
Circuit breaker mounting mode	Fixed
Circuit breaker frame rated current	630 A 400 A

Complementary

Control signal type	Maintained Impulse
Circuit breaker response time	< 700 ms open < 80 ms closed
Maximum operating frequency	4 per minute
Maximum power consumption in VA	500 VA closing 500 VA opening
Locking options description	1 to 3 padlocks Ø 5 to Ø 8 Padlocking in OFF position

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	19.8 cm
Package 1 Width	17.0 cm
Package 1 Length	17.0 cm
Package 1 Weight	3.158 kg
Unit Type of Package 2	S04
Number of Units in Package 2	6
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	19.828 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------