

Tehničke karakteristike proizvoda

Karakteristike

WDE000525

Cedar Plus - dvostruka utičnica sa uzem. -
16A, zaštita, providni poklopac, bela



Osnovne informacije

Range name	Cedar Plus
Tip proizvoda ili komponente	Utičnica
Opis standarda utičnice	Uzemljenje sa strane
Broj utičnica	2
Delivery form	Kompletan proizvod
Additional features	Providan poklopac i zaštita
Cover plate color	Bela

Dopunske informacije

Installation	Nadgradno
Opseg snage	3680 W
Nazivna struja	16 A pri 250 V AC
Kind of terminals	Vijčani priključci
Terminal capacity	2 kabl(ovi) 2,5 mm ²
Wire structure	Fleksibilni Kruti
Dužina ogoljenog dela žice	11 mm
Material of visible parts	PA6 FR850
Završna obrada	Sjajno
Visina	79 mm
Širina	132 mm
Dubina	54 mm
Masa proizvoda	0,196 kg

Okruženje

Sertifikacija proizvoda	VDE
Ip stepen zaštite	IP44

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5,500 cm
Package 1 Width	8,000 cm
Package 1 Length	14,000 cm
Package 1 Weight	201,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	9,500 cm
Package 2 Width	18,500 cm

Package 2 Length	27,000 cm
Package 2 Weight	1,105 kg
Unit Type of Package 3	S03
Number of Units in Package 3	30
Package 3 Height	30,000 cm
Package 3 Width	30,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	7,051 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACh	 REACh Deklaracija
REACh bez SVHC	Da
EU RoHS direktiva	У складу са изузецима
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	18 meseci
-----------	-----------