


Tehničke karakteristike proizvoda

Karakteristike

XA2EW35B1

Žuti kompletni svetleći taster - Ø22 - udubljeni -
24V AC/DC - 1NO



Osnovne informacije

Grupa proizvoda	Easy Harmony XA2
Tip proizvoda ili komponente	Kompletni svetleći taster
Kratko ime uređaja	XA2
Materijal podnožja	Plastika
Prečnik za montiranje	22,5 mm

Dopunske informacije

Prodaja po nedeljivim količinama	1
Tretman zaštite	TC
Radni položaj	Bilo koja pozicija
Centar za fiksiranje	$\geq 30 \times 40$ mm (panel) 1...5 mm
Način fiksiranja	Maticom za fiksiranje preporučeni moment: 2,2 N.m (Us +/- 10 %)
Oblik glave signalne jedinice	Okrugla
Tip glave uređaja	Sa povratkom
Profil glave uređaja	Tamnožuta udubljena
Tip kontakata i sastav	1 NO
Operacija kontakata	Sporo isključenje
Mehanička trajnost	1500000 ciklusa
Povezivanje - priključci	Vijčani priključni blokovi, kapacitet stezaljke: 2×1.5 mm ² Vijčani priključni blokovi, kapacitet stezaljke: 1×2.5 mm ² Faston priključci 6.3 mm Vijčani priključni blokovi, kapacitet stezaljke: 1×0.5 mm ²
Moment pritezanja	0,8 N.m
Zaštita od kratkog spoja	10 A gL osigurač u skladu sa IEC 60269-1
[Ith] dozvoljena termička struja u vazduhu	10 A
[ui] nazivni napon izolacije	600 V u skladu sa IEC 60947-4-1
[uimp] nazivni podnosivi impulsni napon	6 kV u skladu sa IEC 60947-1
[ie] nazivna radna struja	0,27 A pri 250 V, DC-13, Q600 3 A pri 240 V, AC-15, A600
Električna trajnost	500000 Ciklusa, DC-13, 0,2 A pri 110 V, broj operacija <60 ciklusa/min, faktor opterećenja: 0,5 u skladu sa IEC 60947-5-4 500000 ciklusa, DC-13, 3 A pri 230 V, broj operacija <60 ciklusa/min, faktor opterećenja: 0,5 u skladu sa IEC 60947-5-4
Tip signalizacije	Trajna
Svetlosni izvor	LED
Baza sijalice	BA 9s
[us] nazivni napon napajanja	24 V AC/DC 50/60 Hz
Granice napona	19...26 V AC/DC
Struja potrošnje	< 20 mA
Servisni vek	10000 sati
Širina	30 mm

Visina	42 mm
Dubina	74,5 mm
Masa proizvoda	0,056 kg
Boja kapica/glave ili sočiva	Žuta
Tip ručice	Sa povratkom
[us] nazivni napon	24 V

Okruženje

Temperatura okoline za skladištenje	-40...70 °C
Temperatura okoline za rad uređaja	-25...55 °C
Kategorija prenapona	Klasa I u skladu sa IEC 536
Ip stepen zaštite	IP65
Ik stepen zaštite	IK03 u skladu sa IEC 60529
Standardi	IEC 60947-5-1 GB 14048.5 IEC 60947-1 GB 14048.1
Sertifikacija proizvoda	CE[RETURN]CCC
Otpornost na vibracije	10 gn (f= 40...500 Hz) u skladu sa IEC 60068-2-6
Otpornost na udare	70 gn (trajanje = 11 milisekundi) za ubrzanje polovine sinusne periode u skladu sa IEC 60068-2-27


Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4,0 cm
Package 1 Width	11,0 cm
Package 1 Length	16,0 cm
Package 1 Weight	60,0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	40,0 cm
Package 2 Width	160,0 cm
Package 2 Length	110,0 cm
Package 2 Weight	600,0 g
Unit Type of Package 3	S02
Number of Units in Package 3	70
Package 3 Height	15,0 cm
Package 3 Width	30,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	4,3 kg

Održivost ponude

Propis REACH	 REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)  EU RoHS deklaracija
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Dimensions



(e) Clamping thickness: 1 to 6 mm / 0.04 to 0.24 in.

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)


Connection by Screw Clamp Terminals



- (1) Diameter on finished panel or support
(2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.
(3) Ø22.5 mm recommended ($\text{Ø}22.3_0^{+0.4}$) / Ø0.89 in. recommended ($\text{Ø}0.88 \text{ in. }_0^{+0.016}$)

Connections	a in mm	a in in.	b in mm	b in in.
By screw clamp terminals connector	40	1.57	30	1.18
By Faston connectors	45	1.77	32	1.26

Detail of Lug Recess



- (1) Diameter on finished panel or support
(2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.
(3) Ø22.5 mm recommended ($\text{Ø}22.3_0^{+0.4}$) / Ø0.89 in. recommended ($\text{Ø}0.88 \text{ in. }_0^{+0.016}$)