

Tehničke karakteristike proizvoda

Karakteristike

XAPM2502

livena prazna upr. stanica - XAPM - Ø22 -
legura cinka - 2 horizontalna otvora



Osnovne informacije

Grupa proizvoda	Harmony XAP
Tip proizvoda ili komponente	Livena prazna upravljačka stanica
Kratko ime uređaja	XAPM
Namena proizvoda	Za Ø 22 mm upravljačko signalne elemente
Veličina prednje maske proizvoda	80 x 130 mm
Korisna dubina	74,5 mm
Broj otvora	2 izreza
Boja osnova kućišta	Plava
Boja poklopca	Plava
Materijal	Legura cinka
Kablovski uvod	1 otvor sa poklopcem za kablovsku uvodnicu, kapacitet stezaljke: 14 mm 1 otvor bez poklopca za kablovsku uvodnicu, kapacitet stezaljke: 14 mm
Montaža uređaja	Ugradno
Ip stepen zaštite	IP65 u skladu sa IEC 60529 IP69 u skladu sa NF C 20-010 IP69K

Dopunske informacije

Broj vertikalnih redova	1
Masa proizvoda	0,81 kg

Okruženje

Tretman zaštite	TC
Temperatura okoline za skladištenje	-40...70 °C
Temperatura okoline za rad uređaja	-40...70 °C
Kategorija prenapona	Klasa I u skladu sa IEC 60536 Klasa I u skladu sa NF C 20-030

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9,2 cm
Package 1 Width	8,8 cm
Package 1 Length	15,5 cm
Package 1 Weight	1,015 kg


Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) EU RoHS deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Izjava o zaštiti okoliša	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja

Ugovorna garancija

Garancija	18 meseci
-----------	-----------

Dimensions and Fixing




- (1) 1 hole, without blanking plug, for cable gland with 14 mm/0.55 in. maximum clamping capacity
 (2) 1 hole, with blanking plug (protrusion 6 mm/0.23 in.), for cable gland with 14 mm/0.55 in. maximum clamping capacity
 (3) 2 x Ø 5.6 mm/0.22 in. holes, depth 20 mm/0.78 in.
 P Usable depth

a		b		c		G		H		P	
mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
80	3.15	130	5.12	77	3.03	50	1.97	155	4.53	74.5	2.93

Refer to the product characteristics to get the number of cut-outs.

Cut-out interaxis dimensions



b1 Vertical interaxis: 40 mm/1.57 in.