


Tehničke karakteristike proizvoda

Karakteristike

XVC1B5SK

100mm svetlosna kolona CNZPB montaža na bazu - zujalica, trepćuća



Osnovne informacije

Grupa proizvoda	Harmony XVC1
Tip proizvoda ili komponente	Kompletno ožičena monolitna svetleća kolona
Tip baze svetleće kolone ili semafora	5 svetlećih jedinica
Zvučni signal	Zujalica
Prečnik za montiranje	100 mm
Ime komponente	XVC
Svetlosni izvor	LED trajna ili treperenje crvena LED trajna ili treperenje narandžasta LED trajna ili treperenje zelena LED trajna ili treperenje plava LED trajna ili treperenje prozirna
[us] nazivni napon	24 V
Tip kola napajanja	DC
Nivo buke	60...85 dB (stalni ili isprekidani ton) pri 1 m

Dopunske informacije

Materijal	Polikarbonat: svetleća jedinica ABS (akrilonitril-butadien-stiren): bazi PBT + ABS (UL94-V0): gornji poklopac
Montaža proizvoda	Na bazi
Poprečni presek kabla	0,83 Mm ² 0,33 mm ²
Awg mera (američki standard za prečnik žice)	AWG 22 AWG 18
Dužina kabla	500 mm
Označavanje	CE
[uimp] nazivni napon impulsa	0,8 kV
Struja potrošnje	550 mA
Frekvencija treptanja	0,7...3 Hz
Masa proizvoda	1,5 kg
Visina	528 mm

Okruženje

Standardi	IEC 61000-6-2 IEC 61000-6-3 IEC 61000-6-4
Sertifikacija proizvoda	UL
Tretman zaštite	TC
Temperatura okoline za skladištenje	-35...70 °C
Temperatura okoline za rad uređaja	-30...50 °C
Klasa zaštite protiv električnog udara	Klasa II u skladu sa IEC 61140
Ip stepen zaštite	IP54 u skladu sa IEC 60529

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	20,5 cm
Package 1 Width	20,5 cm
Package 1 Length	64,0 cm
Package 1 Weight	2,604 kg
Unit Type of Package 2	P06
Number of Units in Package 2	9
Package 2 Height	77,0 cm
Package 2 Width	80,0 cm
Package 2 Length	60,0 cm
Package 2 Weight	31,936 kg

Održivost ponude

EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Izjava o zaštiti okoliša	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Informacije O Kraju Radnog Veka


Ugovorna garancija

Garancija	18 months
-----------	-----------

Pre-assembled and Pre-wired Tower Light

Dimensions

Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get b dimension.



No. of illuminated units	b in mm	b in in.
1	216	8.50
2	294	11.57
3	372	14.65
4	450	17.72
5	528	20.79

Pre-assembled and Pre-wired Tower Light

Mounting on Horizontal Support (Direct or with Fixing Plate)

Panel cut-out

$$\frac{mm}{in.}$$
