

Tehničke karakteristike proizvoda

Karakteristike

XVC1M2K

100mm svetlosna kolona CN montaža na bazu
100-240VAC



Osnovne informacije

Grupa proizvoda	Harmony XVC1
Tip proizvoda ili komponente	Kompletno ožičena monolitna svetleća kolona
Tip baze svetleće kolone ili semafora	2 svetleće jedinice
Zvučni signal	Bez
Prečnik za montiranje	100 mm
Ime komponente	XVC
Svetlosni izvor	LED trajna ili treperenje crvena LED trajna ili treperenje narandžasta
[us] nazivni napon	100...240 V
Tip kola napajanja	AC

Dopunske informacije

Materijal	Polikarbonat: svetleća jedinica ABS (akrilonitril-butadien-stiren): bazi PBT + ABS (UL94-V0): gornji poklopac
Montaža proizvoda	Na bazi
Poprečni presek kablova	0,33 Mm ² 0,83 mm ²
Awg mera (američki standard za prečnik žice)	AWG 18 AWG 22
Dužina kablova	500 mm
Označavanje	CE
[uimp] nazivni napon impulsa	4 kV
Struja potrošnje	120 mA
Frekvencija treptanja	0,7...3 Hz
Masa proizvoda	1,2 kg
Visina	294 mm

Okruženje

Standardi	IEC 60947-1 IEC 60947-5-1
Sertifikacija proizvoda	UL
Tretman zaštite	TC
Temperatura okoline za skladištenje	-35...70 °C
Temperatura okoline za rad uređaja	-30...50 °C
Klasa zaštite protiv električnog udara	Klasa I u skladu sa IEC 61140
Ip stepen zaštite	IP54 u skladu sa IEC 60529

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	18,0 cm
Package 1 Width	18,0 cm
Package 1 Length	43,0 cm
Package 1 Weight	1,68 kg

Održivost ponude

EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Izjava o zaštiti okoliša	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Informacije O Kraju Radnog Veka
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.


Ugovorna garancija

Garancija	18 meseci
-----------	-----------

Pre-assembled and Pre-wired Tower Light

Dimensions

Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get b dimension.



No. of illuminated units	b in mm	b in in.
1	216	8.50
2	294	11.57
3	372	14.65
4	450	17.72
5	528	20.79

Pre-assembled and Pre-wired Tower Light

Mounting on Horizontal Support (Direct or with Fixing Plate)

Panel cut-out

