



Teknisk informasjon

Produktspekter	Harmony XAC
Produkt eller type komponent	Pendant control station
Kortnavn utstyr	XACB

Komplementær

Tablå type	Dobbeltisolert
Kapslingsmatriale	Glassfiberarmert polyester
Type elektrisk krets	Hovedstrøm Styrekrete
Kapslingstype	Tom kapsling
Antall cut-out	12 cut-outs in 2 rows
Kontrollstasjon farge	Gul
Kabelinngang	Gummihylse med trappet oppføring 22...35 mm
Beskyttelsesbøyle	Uten
Vertikal operatør cut-out center	40 mm
Standarder	IEC 60947-5-1 CSA C22.2 No 14
Produktsertifikater	CSA type 4
Overflatebeskyttelse	TH
Omgivelsestemperatur drift	-25...70 °C
Omgivelsestemperatur for lagring	-40...70 °C
Vibrasjonsmotstand	15 gn (f= 10...500 Hz) i samsvar med IEC 60068-2-6
Støtmotstand	100 gn i samsvar med IEC 60068-2-27
Overspenningskategori	Klasse II i samsvar med IEC 61140
IP-grad	IP65 conforming to IEC 60529
Ik beskyttelsesklasse	IK08 conforming to IEC 62262
Mekanisk levetid	1000000 sykluser
Vekt	1,66 kg

Forpakkingsinformasjon

Enhetstype pakke 1	PCE
Antall enheter i pakke 1	1
Pakke 1 Høyde	9,500 cm
Pakke 1 Bredde	66,000 cm
Pakke 1 Vekt	16,000 cm
Package 1 Weight	1,800 kg
Enhetstype pakke 2	P06
Antall enheter i pakke 2	15
Pakke 2 Høyde	75,000 cm
Pakke 2 Bredde	60,000 cm

Pakke 2 Lengde	80,000 cm
Pakke 2 Vekt	40,000 kg

Bærekraftig

REACH-regelverk	 REACH-erklæring
REACH fri for SVHC	Ja
EU RoHS-direktiv	Proaktivt i samsvar (Produktet inngår ikke i EUs RoHS direktivet)  EU RoHS-erklæring
Fri for giftige tungmetaller	Ja
Kvikksølvfri	Ja
Kinas RoHS-forskrift	 Kinas RoHS-Erklæring
Informasjon om RoHS-unntak	 Ja
WEEE	Innen EU må produktet avhendes i henhold til bestemte regler for avfallshåndtering og aldri kastes som husholdningsavfall.

Logistisk informasjon


Opprinnelsesland	CZ
------------------	----

Garantiperiode

Garanti	18 months
---------	-----------

Dimensions

Below drawing shows a product with 12 cut-outs. Select the number of cut-outs according to the product characteristics in order to get b, b1 and c dimensions.




Dimensions in mm

Number of cut-outs	2	4	6	8	12
b	409	499	589	679	593
b1	220	310	400	490	404
c	98	98	98	98	158
d	40	40	40	40	40

Dimensions in in.

Number of cut-outs	2	4	6	8	12
b	16.10	19.64	23.19	26.73	23.35
b1	8.66	12.20	15.75	19.29	15.90
c	3.86	3.86	3.86	3.86	6.22
d	1.57	1.57	1.57	1.57	1.57


Protective cable sleeves



(1) Internal Ø


Control of Single-Speed Reversing Motor

With XESD1181 contact block, to be ordered separately



Control of 2-Speed Reversing Motor


With XESD1281 contact block, to be ordered separately




KM High speed contactor

Control of Single-Speed Reversing Motor 2-Phase Switching

With XESD1191 contact block, to be ordered separately




Combined with 3-pole isolating block XACS399 or XACS3991, shown in the unoperated position (pendant station “supplied”), fitted with key release trigger action latching Emergency stop operator.




Control of 2-Speed Reversing Motor 2-Phase Switching

With XESD1291 contact block, to be ordered separately



Control of Single-Speed Reversing Motor 3-Phase switching, Reversing by 2-Phase Inversion

With XESD2201 contact block, to be ordered separately



Control of Single-Speed Reversing Motor 3-Phase switching, Reversing by 2-Phase Inversion

With XESD2241 contact block, to be ordered separately

