

## Tehničke karakteristike proizvoda

### Karakteristike

## XVC6B25SK

60mm svetlosna kolona RO montaža na bazu  
zujalica, trepćuća



### Osnovne informacije

|                                       |                                                                           |
|---------------------------------------|---------------------------------------------------------------------------|
| Grupa proizvoda                       | Harmony XVC6                                                              |
| Tip proizvoda ili komponente          | Kompletno ožičena monolitna svetleća kolona                               |
| Tip baze svetleće kolone ili semafora | 2 svetleće jedinice                                                       |
| Zvučni signal                         | Zujalica                                                                  |
| Prečnik za montiranje                 | 60 mm                                                                     |
| Ime komponente                        | XVC                                                                       |
| Svetlosni izvor                       | LED trajna ili treperenje crvena<br>LED trajna ili treperenje narandžasta |
| [us] nazivni napon                    | 24 V                                                                      |
| Tip kola napajanja                    | AC/DC                                                                     |
| Nivo buke                             | 70...85 dB (stalni ili isprekidani ton) pri 1 m                           |

### Dopunske informacije

|                                              |                                                                                                                    |
|----------------------------------------------|--------------------------------------------------------------------------------------------------------------------|
| Materijal                                    | Polikarbonat: svetleća jedinica<br>ABS (akrilonitril-butadien-stiren): bazi<br>PBT + ABS (UL94HB): gornji poklopac |
| Montaža proizvoda                            | Na bazi                                                                                                            |
| Poprečni presek kabla                        | 0,33 mm <sup>2</sup>                                                                                               |
| Awg mera (američki standard za prečnik žice) | AWG 22                                                                                                             |
| Dužina kabla                                 | 850 mm                                                                                                             |
| Označavanje                                  | CE                                                                                                                 |
| [uimp] nazivni napon impulsa                 | 0,8 kV                                                                                                             |
| Struja potrošnje                             | 90 mA                                                                                                              |
| Frekvencija osnovnog harmonika               | 2,23 kHz                                                                                                           |
| Frekvencija treptanja                        | 1 Hz                                                                                                               |
| Masa proizvoda                               | 0,25 kg                                                                                                            |
| Visina                                       | 160,8 mm                                                                                                           |

### Okruženje

|                                        |                                                          |
|----------------------------------------|----------------------------------------------------------|
| Standardi                              | IEC 61000-6-4<br>IEC 61000-6-3<br>IEC 61000-6-2          |
| Sertifikacija proizvoda                | UL                                                       |
| Tretman zaštite                        | TC                                                       |
| Temperatura okoline za skladištenje    | -35...70 °C                                              |
| Temperatura okoline za rad uređaja     | -10...50 °C                                              |
| Klasa zaštite protiv električnog udara | Klasa II u skladu sa IEC 61140                           |
| Ip stepen zaštite                      | IP54 instalaciji na ravnu površinu u skladu sa IEC 60529 |

## Pakovanje

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Height             | 8,6 cm   |
| Package 1 Width              | 8,8 cm   |
| Package 1 Length             | 50,2 cm  |
| Package 1 Weight             | 480,0 g  |
| Unit Type of Package 2       | S04      |
| Number of Units in Package 2 | 12       |
| Package 2 Height             | 30,0 cm  |
| Package 2 Width              | 40,0 cm  |
| Package 2 Length             | 60,0 cm  |
| Package 2 Weight             | 7,109 kg |

## Održivost ponude

|                              |                                                                              |
|------------------------------|------------------------------------------------------------------------------|
| EU RoHS direktiva            | Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) |
| Bez žive                     | Da                                                                           |
| RoHS regulativa za Kinu      | <a href="#">RoHS Deklaracija Za Kinu</a>                                     |
| Informacije o RoHS izuzecima | <a href="#">Da</a>                                                           |
| Izjava o zaštiti okoliša     | <a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>                    |
| Profil cirkularnosti         | <a href="#">Informacije O Kraju Radnog Veka</a>                              |


## Ugovorna garancija

|           |           |
|-----------|-----------|
| Garancija | 18 meseci |
|-----------|-----------|

## Pre-assembled and Pre-wired Tower Light

### Dimensions

Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get b dimension.



| No. of illuminated units | b (mm) | b (in.) |
|--------------------------|--------|---------|
| 1 stage                  | 120.8  | 4.76    |
| 2 stages                 | 160.8  | 6.33    |
| 3 stages                 | 200.8  | 7.90    |
| 4 stages                 | 240.8  | 9.48    |
| 5 stages                 | 280.8  | 11.06   |

---

Pre-assembled and Pre-wired Tower Light

---

Mounting on Horizontal Support (Direct or with Fixing Plate)

Panel cut-out

