

Tehničke karakteristike proizvoda

Karakteristike

XVC6M45SK

60mm svetlosna kolona CNZP montaža na bazu - zujalica, trepćuća 100-240VAC



Osnovne informacije

Grupa proizvoda	Harmony XVC6
Tip proizvoda ili komponente	Kompletno ožičena monolitna svetleća kolona
Tip baze svetleće kolone ili semafora	4 svetleće jedinice
Zvučni signal	Zujalica
Prečnik za montiranje	60 mm
Ime komponente	XVC
Svetlosni izvor	LED trajna ili treperenje crvena LED trajna ili treperenje narandžasta LED trajna ili treperenje zelena LED trajna ili treperenje plava
[us] nazivni napon	100...240 V
Tip kola napajanja	AC
Nivo buke	70...85 dB (stalni ili isprekidani ton) pri 1 m

Dopunske informacije

Materijal	Polikarbonat: svetleća jedinica ABS (akrilonitril-butadien-stiren): bazi PBT + ABS (UL94-V0): gornji poklopac
Montaža proizvoda	Na bazi
Poprečni presek kabla	0,83 Mm ² 0,33 mm ²
Awg mera (američki standard za prečnik žice)	AWG 18 AWG 22
Dužina kabla	850 Mm 750 mm
Označavanje	CE
[uimp] nazivni napon impulsa	4 kV
Struja potrošnje	100 mA
Frekvencija osnovnog harmonika	2,23 kHz
Frekvencija treptanja	1 Hz
Masa proizvoda	0,65 kg
Visina	352 mm

Okruženje

Standardi	EN/IEC 60947-5-1 EN/IEC 60947-1
Sertifikacija proizvoda	UL
Tretman zaštite	TC
Temperatura okoline za skladištenje	-35...70 °C
Temperatura okoline za rad uređaja	-10...50 °C
Klasa zaštite protiv električnog udara	Klasa I u skladu sa EN/IEC 61140
Ip stepen zaštite	IP54 instalaciji na ravnu površinu u skladu sa EN/IEC 60529

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8,5 cm
Package 1 Width	8,5 cm
Package 1 Length	51,0 cm
Package 1 Weight	806,0 g
Unit Type of Package 2	S04
Number of Units in Package 2	12
Package 2 Height	30,0 cm
Package 2 Width	40,0 cm
Package 2 Length	60,0 cm
Package 2 Weight	10,924 kg

Održivost ponude

EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Izjava o zaštiti okoliša	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Informacije O Kraju Radnog Veka
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.


Ugovorna garancija

Garancija	18 meseci
-----------	-----------

Pre-assembled and Pre-wired Tower Light

Dimensions

Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get b dimension.



No. of illuminated units	b (mm)	b (in.)
1 stage	232	9.13
2 stages	272	10.71
3 stages	312	12.28
4 stages	352	13.86
5 stages	392	15.43

Pre-assembled and Pre-wired Tower Light

Mounting on Horizontal Support (Direct or with Fixing Plate)

Panel cut-out

