

Tehničke karakteristike proizvoda

Karakteristike

A9L65101

iPRD65r modularni odvodnik prenapona - 1P - 350V - sa daljinskom signal.



Osnovne informacije

Grupa proizvoda	Acti9
Ime proizvoda	Acti 9 iPRD
Tip proizvoda ili komponente	Izvlačivi odvodnik prenapona
Kratko ime uređaja	iPRD65r
Primena uređaja	Razvod električne energije
Standardi	EN 61643-11:2012 IEC 61643-11:2011
Sertifikacija proizvoda	CE
Oznake kvaliteta	KEMA-KEUR NF
Broj polova	1P
Daljinska signalizacija	Sa
Signalni kontakt	1 SD (1 C/O)
Tip odvodnika prenapona	Električna distributivna mreža
Sistem uzemljenja	IT 230 TN-C

Dopunske informacije

Tip klase odvodnika prenapona	Tip 2
Tehnologija odvodnika prenapona	MOV
[ue] nazivni napon	230/400 V AC (+/- 10 %) pri 50/60 Hz
[In] nominalna struja pražnjenja	Asimetrični režim: 20 kA (L/PE) Asimetrični režim: 20 kA (N/PE)
[Imax] maksimalna struja pražnjenja	Asimetrični režim: 65 kA L/PE
[uc] maksimalni stalni radni napon	Asimetrični režim: 350 V L/PE Asimetrični režim: 350 V N/PE
Maksimalni [up] napon naponske zaštite	Asimetrični režim <1,5 kV tip 2 L/PE
[ut] privremeni prenapon	337 V L/N 5 s podnošljivo 1200 V N/PE 200 ms sigurnosni režim
Tip rastavljača	Pridruženi prekidač iC60N 50 A kriva C - Icu 10 kA Pridruženi prekidač iC60H 50 A kriva C - Icu 15 kA Pridruženi prekidač NG125N 50 A kriva C - Icu 25 kA Pridruženi prekidač NG125H 100 A kriva C - Icu 36 kA Pridruženi prekidač NG125L 100 A kriva C - Icu 50 kA Pridruženi osigurač gG 80 A - Icu 50 kA
Signal napona	0.25 A/250 V AC 50/60 Hz
Način montaže	Sistemom na klik (DIN šina)
9 mm redovi	2
Visina	85 mm
Širina	18 mm
Dubina	69 mm
Masa proizvoda	0,136 kg
Boja	Bela (RAL 9003)
[Ipe] struja curenja	0,003 MA 0,6 mA

Informacije navedene u ovoj dokumentaciji predstavljaju opšti opis odnosno tehničke karakteristike performansi proizvoda. Dokumentacija nije namenjena da bude zamena za niti se može koristiti za određivanje prikladnosti i pouzdanosti proizvoda za specifičnu krajnju primenu. Dužnost je korisnika odnosno integratora da izvrši primerenu i sveobuhvatnu analizu rizika, procenu i proveru proizvoda u pogledu odgovarajuće specifične primene ili načina korišćenja. Ni Schneider Electric Industries SAS ni njegova povezana ili zavisna društva neće snositi odgovornost za zloupotrebu ovdanavedenih informacija.

Povezivanje - priključci	Tunelski priključak (donji) 2,5...35 mm ² Tunelski priključak (gornji) 2,5...35 mm ²
Moment pritezanja	2,5 N.m

Okruženje

Ik stepen zaštite	IK03 u skladu sa IEC 62262
Relativna vlažnost	5...95 %
Nadmorska visina za rad	2000 m
Temperatura okoline za rad uređaja	-25...60 °C
Temperatura okoline za skladištenje	-40...85 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2 cm
Package 1 Width	7 cm
Package 1 Length	9 cm
Package 1 Weight	158 g
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	8 cm
Package 2 Width	10 cm
Package 2 Length	27,5 cm
Package 2 Weight	1,987 kg
Unit Type of Package 3	S03
Number of Units in Package 3	108
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	18,596 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACh	REACh Deklaracija
REACh bez SVHC	Da
EU RoHS direktiva	Usaglašeno EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Izjava o zaštiti okoliša	Profil Ekološke Prihvatljivosti Proizvoda
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	18 months
-----------	-----------