

Tehničke karakteristike proizvoda

Karakteristike

RSB2A080P7

interfejs utični relej - Zelio RSB - 2 C/O - 230 V AC - 8 A

Osnovne informacije

Grupa proizvoda	Harmony Electromechanical Relays
Ime serije	Interfejs relej
Tip proizvoda ili komponente	Utični relej
Kratko ime uređaja	RSB
Tip kontakata i sastav	2 C/O
Operacija kontakata	Standardna
Napon upravljačkog kola	230 V AC 50/60 Hz
[ithe] dozvoljena termička struja u ormanu	8 A pri -40...40 °C
Statusne led lampice	Bez
Tip upravljanja	Bez tastera

Dopunske informacije

Oblik pina	Ravni (PCB tip)
Average coil resistance	33000 Ω mreža: AC pri 20 °C +/- 10 %
[ue] nazivni napon	184...345 V AC 50/60 Hz
[ui] nazivni napon izolacije	400 V u skladu sa IEC 60947
[uimp] nazivni podnosivi impulsni napon	3,6 kV u skladu sa IEC 61000-4-5
Materijal kontakata	Legura srebra (AgNi)
[ie] nazivna radna struja	4 A (AC-1/DC-1) NC u skladu sa IEC 8 A (AC-1/DC-1) NO u skladu sa IEC
Minimalna struja preklapanja	10 mA
Maksimalni napon preklapanja	300 V DC u skladu sa IEC
Minimum switching voltage	12 V
Maksimalna moć preklapanja	2000 VA/224 W
Resistive rated load	8 A pri 250 V AC 8 A pri 28 V DC
Minimalna preklopna moć	120 mW pri 10 mA, 12 V
Broj operacija	<= 600 ciklusa/h pod opterećenjem <= 18000 ciklusa/h bez opterećenja
Mehanička trajnost	5000000 ciklusa
Električna trajnost	100000 Ciklusa, 8 A pri 250 V, AC-1 NO 100000 ciklusa, 4 A pri 250 V, AC-1 NC
Vreme uključanja/isključanja	20 ms uključanje 20 ms reset
Average coil consumption	0,75 VA AC
Prag napona propada	>= 0.15 U _c AC
Sigurnosni podaci o pouzdanosti	B10d = 100000
Kategorija zaštite	RT I
Test nivoi	Nivo A grupna ugradnja
Radni položaj	Bilo koja pozicija
Masa proizvoda	0,014 kg
Prodaja po nedeljivim količinama	10
Prezentacija uređaja	Kompletan proizvod





Okruženje

Dielektrična snaga	1000 V AC između kontakata 2500 V AC između polova 5000 V AC između kalema i kontakta
Standardi	CSA C22.2 No 14 UL 508 IEC 61810-1
Sertifikacija proizvoda	CSA[RETURN]EAC[RETURN]UL
Temperatura okoline za skladištenje	-40...85 °C
Otpornost na vibracije	+/- 1 mm (f= 10...55 Hz) conforming to IEC 60068-2-6
Ip stepen zaštite	IP40 conforming to IEC 60529
Otpornost na udare	10 gn (trajanje = 11 milisekundi) za kada uređaj nije u radu u skladu sa IEC 60068-2-27 5 gn (trajanje = 11 milisekundi) za u radu u skladu sa IEC 60068-2-27
Temperatura okoline za rad	-40...70 °C (AC)

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1,200 cm
Package 1 Width	2,000 cm
Package 1 Length	2,900 cm
Package 1 Weight	13,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	1,700 cm
Package 2 Width	2,500 cm
Package 2 Length	31,100 cm
Package 2 Weight	146,000 g
Unit Type of Package 3	S01
Number of Units in Package 3	350
Package 3 Height	15,000 cm
Package 3 Width	15,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	5,240 kg

Održivost ponude

Pakovanje bez plastike	Da
Pakovanje sa recikliranim kartonom	Da
Uredba REACh	 REACh Deklaracija
Bez SVHC-a REACh	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)  EU RoHS deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
Održivo pakovanje	Da
Informacije o izuzeću od RoHS	 Da
Kina RoHS regulacija	 RoHS Deklaracija Za Kinu
WEEE	Proizvod se mora odložiti na tržišta Evropske unije nakon posebnog sakupljanja otpada i nikada ne završiti u kanti za smeće
Povraćaj	No
Emisija ugljenika (kg CO2 eq.)	12

Ugovorna garancija

Garancija	18 meseci
-----------	-----------