



Main

Range	ComPact
Product name	ComPacT INS
Product or component type	Switch disconnecter
Poles description	4P
Network type	AC DC
Network frequency	50/60 Hz
[Ie] rated operational current	AC-22A: 125 A AC 50/60 Hz 220/240 V AC-22A: 125 A AC 50/60 Hz 380/415 V AC-22A: 125 A AC 50/60 Hz 440/480 V 2 poles in series AC-22A: 125 A AC 50/60 Hz 500 V 2 poles in series AC-22A: 125 A AC 50/60 Hz 660/690 V 4 poles in series AC-23A: 125 A AC 50/60 Hz 220/240 V 4 poles in series AC-23A: 125 A AC 50/60 Hz 380/415 V AC-23A: 125 A AC 50/60 Hz 440/480 V AC-23A: 125 A AC 50/60 Hz 500 V AC-23A: 80 A AC 50/60 Hz 660/690 V DC-22A: 125 A DC 50/60 Hz 125 V 2 poles in series DC-23A: 125 A DC 50/60 Hz 125 V 2 poles in series DC-22A: 125 A DC 50/60 Hz 250 V 4 poles in series DC-23A: 125 A DC 50/60 Hz 250 V 4 poles in series
[Ui] rated insulation voltage	750 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
[Ith] conventional free air thermal current	125 A at 60 °C
[Icm] rated short-circuit making capacity	154 kA with upstream protection circuit breaker 690 V AC at 50/60 Hz 20 kA switch-disconnector alone 690 V AC at 50/60 Hz
[Ue] rated operational voltage	250 V DC 690 V AC 50/60 Hz
Suitability for isolation	Yes
Contact position indicator	Yes
Visible break	No
Pollution degree	3

Complementary

Control type	Rotary handle
Handle colour	Black
Mounting mode	Fixed
Mounting support	DIN rail Plate
Upside connection	Front
Downside connection	Front

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company Schneider Electric. This information is not intended to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Maximum power	AC-23: 55 kW at 440 V AC 50/60 Hz AC-23: 37 kW at 220/240 V AC 50/60 Hz AC-23: 55 kW at 380/415 V AC 50/60 Hz AC-23: 75 kW at 500/525 V AC 50/60 Hz AC-23: 75 kW at 660/690 V AC 50/60 Hz
Rated duty	Uninterrupted
Intermittent duty class	Class 120 - 60 %
Enclosure dimensions for lthe	260 mm x 160 mm x 55 mm
[I _{cw}] rated short-time withstand current	0.01 kA during 30 s conforming to IEC 60947-3 1.23 kA during 20 s conforming to IEC 60947-3 3.175 kA during 3 s conforming to IEC 60947-3 5.5 kA during 1 s conforming to IEC 60947-3
Mechanical durability	15000 cycles
Electrical durability	AC-22A: 1500 cycles 220/240 V AC 50/60 Hz AC-22A: 1500 cycles 380/415 V AC 50/60 Hz 4 poles in series AC-22A: 1500 cycles 440 V AC 50/60 Hz AC-22A: 1500 cycles 500 V AC 50/60 Hz AC-23A: 1500 cycles 220/240 V AC 50/60 Hz AC-23A: 1500 cycles 380/415 V AC 50/60 Hz AC-23A: 1500 cycles 440 V AC 50/60 Hz AC-23A: 1500 cycles 500 V AC 50/60 Hz DC-22A: 1500 cycles 250 V DC 50/60 Hz 4 poles in series DC-23A: 1500 cycles 250 V DC 50/60 Hz 4 poles in series AC-22A: 1500 cycles 690 V AC 50/60 Hz AC-23A: 1500 cycles 690 V AC 50/60 Hz 4 poles in series
Connection pitch	30 mm
Height	100 mm
Width	135 mm
Depth	62.5 mm
Net weight	0.9 kg

Environment

Standards	IEC 60947-3 IEC 60947-1
Product certifications	CCC[RETURN]KEMA-KEUR
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to EN 50102
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.500 cm
Package 1 Width	11.600 cm
Package 1 Length	15.000 cm
Package 1 Weight	1.121 kg
Unit Type of Package 2	S03
Number of Units in Package 2	10
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	11.596 kg
Unit Type of Package 3	P12
Number of Units in Package 3	80
Package 3 Height	43.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	106.000 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------