



Teknisk informasjon

Produktspekter	Harmony XB6
Produkt eller type komponent	Complete body for pilot lights
Kortnavn utstyr	ZB6
Salg per udelelig kvantitet	5
Tilkoblingsklemmer	Pins for kretskort, forbindelses størrelse: 1 x 0,5 mm
Lyskilde	LED
Pæreholder	Innebygget LED
Lysblokkforsyning	Direkte
Lyskildefarge	Grønn
[Us] matespenning	12...24 V AC/DC

Komplementær

Vekt	0,003 kg
Driftsposisjon	Alle posisjoner
[Ui] isolasjonsspenning	250 V (forurensningsgrad 3) i samsvar med IEC 60947-1
[Uimp] Nominell impuls-spenning	4 kV i samsvar med IEC 60947-1
Signaltype	Klar
Spenningsgrenser	6...30 V AC/DC
Strømforbruk	15 mA
Motstand mot spenningsvariasjon	1 kV i kontakt i samsvar med IEC 61000-4-5 2 kV i friluft i samsvar med IEC 61000-4-5

Miljø

Overflatebeskyttelse	TC
Omgivelsestemperatur for lagring	-40...70 °C
Omgivelsestemperatur drift	-25...70 °C
Beskyttelsesgrad mot elektrisk støt	Klasse II i samsvar med IEC 61140
Standarder	JIS C 852 IEC 60947-5-5 JIS C 4520 UL 508 CSA C22.2 No 14 IEC 60947-5-1 IEC 60947-1
Produktsertifikater	UL[RETURN]GOST[RETURN]CSA[RETURN]CCC
Vibrasjonsmotstand	+/- 3 mm (f= 2...500 Hz) i samsvar med IEC 60068-2-6 5 gn (f= 2...500 Hz) i samsvar med IEC 60068-2-6
Støtmotstand	30 gn (varighet = 18 ms) for halvsinuskurve akselerasjon i samsvar med IEC 60068-2-27 50 gn (varighet = 11 ms) for halvsinuskurve akselerasjon i samsvar med IEC 60068-2-27
Motstand mot raske transienter	2 kV i samsvar med IEC 61000-4-4
Motstand mot elektromagnetiske felt	10 V/m i samsvar med IEC 61000-4-3
Motstand mot elektrostatisk utladning	6 KV ved kontakt (på metalldeler) i samsvar med IEC 61000-2-6 8 kV i fri luft (i isolerende deler) i samsvar med IEC 61000-2-6
Elektromagnetiske utslipp	Klasse B i samsvar med IEC 55011

Forpakkingsinformasjon

Enhetstype pakke 1	PCE
Antall enheter i pakke 1	1
Pakke 1 Høyde	0,600 cm
Pakke 1 Bredde	1,700 cm
Pakke 1 Vekt	4,700 cm
Package 1 Weight	2,200 g
Enhetstype pakke 2	BB1
Antall enheter i pakke 2	5
Pakke 2 Høyde	2,000 cm
Pakke 2 Bredde	3,000 cm
Pakke 2 Lengde	6,500 cm
Pakke 2 Vekt	16,000 g
Enhetstype pakke 3	S01
Antall enheter i pakke 3	660
Pakke 3 Høyde	15,000 cm
Pakke 3 Bredde	15,000 cm
Pakke 3 Lengde	40,000 cm
Pakke 3 Vekt	2,275 kg

Bærekraftig

REACH-regelverk	 REACH-erklæring
EU RoHS-direktiv	Proaktivt i samsvar (Produktet inngår ikke i EUs RoHS direktivet)
Kvikksølvfri	Ja
Kinas RoHS-forskrift	 Kinas RoHS-Erklæring
Informasjon om RoHS-unntak	 Ja
Produktets livssyklus	Ingen behov for spesifikke resirkuleringsprosedyrer
WEEE	Innen EU må produktet avhendes i henhold til bestemte regler for avfallshåndtering og aldri kastes som husholdningsavfall.

Logistisk informasjon


Opprinnelsesland	FR
------------------	----

Garantiperiode

Garanti	18 months
---------	-----------


Body for Pilot Light

Dimensions



b 15.5 mm/0.61 in.

Front Panel Cut-out (Viewed from Installer's Side)



- A 24 mm/0.94 in. minimum for rectangular heads, 18 mm/0.71 in. minimum for square or circular heads
- B 18 mm/0.71 in. minimum
- (1) 6 x Ø 1.1 mm / 6 x Ø 0.04 in. holes.
- (2) 1 x Ø 2.6⁰_{-0.2} mm / 1 x Ø 0.10⁰_{-0.008} in. hole for locating pin, only when using socket adaptor ZB6Y010.
- (3) 1 x Ø 3.2⁰_{-0.2} mm / 1 x Ø 0.13⁰_{-0.008} in. hole for fixing of printed circuit board onto the front panel using body bracket ZB6Y011.
- This hole must be drilled on the left-hand side, when heads are positioned at the normal angle. Fit a body bracket ZB6Y011 every 72 mm/2.83 in. maximum for cut-outs on 24 mm/0.94 in. centres (rectangular heads) and 54 mm/2.13 in. maximum for cut-outs on 18 mm/0.71 in. centres (square or circular heads).


General tolerances of the panel and printed circuit board: T1, T2: T1 + T2 = 0.3 mm/0.01 in. maximum.

Installation precautions:

Thickness of printed circuit board: 1.6 mm/0.06 in. minimum.


Mounting with Body Bracket

With socket adaptor ZB6Y010



- (1) Head
- (2) Nut
- (3) Body
- (4) Body bracket
- (5) Contact block
- (6) Socket adaptor
- (7) Panel
- (8) Printed circuit

Direct mounting without socket adaptor ZB6Y010



- (1) Head
- (2) Nut
- (3) Body
- (4) Body bracket
- (5) Contact block
- (6) Panel
- (7) Printed circuit