





Osnovne informacije

Grupa proizvoda	TeSys
Ime proizvoda	TeSys LC1D.K TeSys Deca
Tip proizvoda ili komponente	Kontaktor za kondenzatorske baterije
Kratko ime uređaja	LC1DWK
Primena uređaja	Upravljanje
Primena kontaktora	Korekcija faktora snage
Kategorija upotrebe	AC-6B
Broj polova	3P
Power pole contact composition	3 NO
[ue] nazivni napon	Kolo napajanja: 690 V AC 50/60 Hz
Reaktivna snaga	35 Kvar pri 230 V AC 50 Hz pri <60 °C 63 Kvar pri 400 V AC 50 Hz pri <60 °C 67 Kvar pri 440 V AC 50 Hz pri <60 °C 104 Kvar pri 690 V AC 50 Hz pri <60 °C 30 Kvar pri 230 V AC 60 Hz pri <60 °C 60 Kvar pri 460 V AC 60 Hz pri <60 °C 80 kvar pri 575 V AC 60 Hz pri <60 °C
Tip upravljačkog kola	AC pri 50/60 Hz
Napon upravljačkog kola	230 V AC 50/60 Hz
Sastav pomoćnog kontakta	1 NO + 2 NC trenutno
Električna trajnost	300000 Ciklusa pri Ue 400 V 200000 ciklusa pri Ue 690 V
Nosači za montažu	DIN šina Ploča
Standardi	EN/IEC 60947-1 EN/IEC 60947-4-1 UL 60947-4-1 CSA C22.2 No 60947-4-1
Sertifikacija proizvoda	IECEE CB Scheme[RETURN]UL[RETURN]CSA[RETURN]UKCA
Povezivanje - priključci	Upravljačko kolo: vijčani priključni blokovi 1 1... 4 mm ² - cable stiffness: jednožični Upravljačko kolo: vijčani priključni blokovi 2 1... 4 mm ² - cable stiffness: jednožični Upravljačko kolo: vijčani priključni blokovi 1 1... 4 mm ² - cable stiffness: fleksibilni bez kablovskog završetka Upravljačko kolo: vijčani priključni blokovi 2 1... 4 mm ² - cable stiffness: fleksibilni bez kablovskog završetka Upravljačko kolo: vijčani priključni blokovi 1 1... 4 mm ² - cable stiffness: fleksibilni sa kablovskim završetkom Upravljačko kolo: vijčani priključni blokovi 2 1... 2,5 mm ² - cable stiffness: fleksibilni sa kablovskim završetkom Kolo napajanja: priključak 1 4...50 mm ² - cable stiffness: jednožični Kolo napajanja: priključak 2 4...25 mm ² - cable stiffness: jednožični Kolo napajanja: priključak 1 4...50 mm ² - cable stiffness: fleksibilni bez kablovskog završetka Kolo napajanja: priključak 2 4...25 mm ² - cable stiffness: fleksibilni bez kablovskog završetka Kolo napajanja: priključak 1 4...50 mm ² - cable stiffness: fleksibilni sa kablovskim završetkom Kolo napajanja: priključak 2 4...16 mm ² - cable stiffness: fleksibilni sa kablovskim završetkom
Moment pritezanja	Kolo napajanja: 12 N.m - na priključak Upravljačko kolo: 1,7 N.m - na vijčani priključni blokovi
Maksimalni radni ciklus	240 ciklusa/h

Dopunske informacije

Tip pomoćnog kontakta	Tip mehanički povezani 1 NO + 2 NC u skladu sa IEC 60947-5-1
-----------------------	--

Okruženje

Ip stepen zaštite	IP20 prednja strana u skladu sa IEC 60529
Temperatura okoline za rad uređaja	-5...60 °C
Temperatura okoline za skladištenje	-60...80 °C
Nadmorska visina za rad uređaja	0...3000 m
Visina	180 mm
Širina	85 mm
Dubina	154 mm
Masa proizvoda	1,65 kg

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13,000 cm
Package 1 Width	17,000 cm
Package 1 Length	18,500 cm
Package 1 Weight	1,790 kg
Unit Type of Package 2	S04
Number of Units in Package 2	8
Package 2 Height	30,000 cm
Package 2 Width	40,000 cm
Package 2 Length	60,000 cm
Package 2 Weight	14,970 kg
Unit Type of Package 3	P06
Number of Units in Package 3	48
Package 3 Height	75,000 cm
Package 3 Width	80,000 cm
Package 3 Length	60,000 cm
Package 3 Weight	97,820 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACh	 REACh Deklaracija
REACh bez SVHC	Da
EU RoHS direktiva	Usaglašeno  EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	18 meseci
-----------	-----------