



Osnovne informacije

Grupa proizvoda	Harmony Control Relays
Tip releja	Multifunkcijski kontrolni relej
Tip proizvoda ili komponente	3-phase control relay
Specifične primene proizvoda	Za trofazno napajanje
Ime releja	RM17TA
Nadzirani parametri releja	Asimetrija Redosled faza Detekcija gubitak faze
Vremensko kašnjenje	Podesivo 0.1...10 s, +/- 10 % vrednosti pune skale Tt- time delay upon fault
Preklopna moć u va	1250 VA
Opseg merenja	208...480 V AC
Tip kontakata i sastav	1 C/O
[uc] napon upravljačkog kola	208...480 V

Dopunske informacije

Vreme reseta	1500 milisekundi kašnjenje
Maksimalni napon preklapanja	250 V AC 250 V DC
Minimalna struja preklapanja	10 mA pri 5 V DC
Maksimalna struja preklapanja	5 A AC 5 A DC
[Un] rated nominal voltage	, self-powered
Granice napona	183...528 V AC
Ograničenje napona upravljačkog kola	- 12 % + 10 % Un
Snaga potrošnje u va	0...22 VA pri 400 V AC 50 Hz
Frekvencija upravljačkog kola	50...60 Hz +/- 10 %
Izlazni kontakti	1 C/O
Nazivna izlazna struja	5 A
Granice merenog napona	183...528 V AC
Histerezis	2 %
Kašnjenje pri uključivanju	650 milisekundi
Maksimalni ciklus merenja	150 milisekundi ciklus merenja kao prava efektivna vrednost
Opseg napona	208...480 V međufazno
Podešavanje praga asimetrije	5...15 % izabranog Un
Tačnost ponavljanja	0,5 % za ulazno i kolo merenja 3 % za kašnjenje
Greška merenja	< 0.05 %/°C sa promenom temperature < 1 % preko celog opsega sa promenom napona
Osetljivost gubitka faze	0.7 Un
Vreme odziva	< 200 ms (u slučaju greške)
Označavanje	CE
Kategorija prenapona	III u skladu sa IEC 60664-1
Otpornost izolacije	> 500 MOhm pri 500 V DC u skladu sa IEC 60255-5 > 500 MOhm pri 500 V DC u skladu sa IEC 60664-1
[ui] nazivni napon izolacije	400 V u skladu sa IEC 60664-1

Frekvencija napajanja	50/60 Hz +/- 10 %
Radni položaj	Bilo koja pozicija bez smanjenja karakteristika
Povezivanje - priključci	Vijčani priključci, 1 x 0.5...1 x 4 mm ² (AWG 20...AWG 11) jednožični bez kablovskog završetka Vijčani priključci, 2 x 0.5...2 x 2.5 mm ² (AWG 20...AWG 14) jednožični bez kablovskog završetka Vijčani priključci, 1 x 0.2...1 x 2.5 mm ² (AWG 24...AWG 12) fleksibilni sa kablovskim završetkom Vijčani priključci, 2 x 0.2...2 x 1.5 mm ² (AWG 24...AWG 16) fleksibilni sa kablovskim završetkom
Moment pritezanja	0,6...1 N.m u skladu sa IEC 60947-1
Materijal kućišta	Samogasiva plastika
Lokalna signalizacija	Zauključen uređaj: LED (zeleni) Zarelej ON: LED (žuta)
Držač za montažu	35 mm simetrična DIN šina u skladu sa IEC 60715
Električna trajnost	100000 ciklusa
Mehanička trajnost	30000000 ciklusa
Broj operacija	<= 360 operacija/h punog opterećenja
Kategorija upotrebe	AC-12 u skladu sa IEC 60947-5-1 AC-13 u skladu sa IEC 60947-5-1 AC-14 u skladu sa IEC 60947-5-1 AC-15 u skladu sa IEC 60947-5-1 DC-12 u skladu sa IEC 60947-5-1 DC-13 u skladu sa IEC 60947-5-1
Sigurnosni podaci o pouzdanosti	MTTFd = 502.2 godine B10d = 470000
Širina	17,5 mm
Masa proizvoda	0,13 kg
Tip upravljanja	Bez test tastera

Okruženje

Elektromagnetna kompatibilnost	Standard emisije za industrijske sredine conforming to IEC 61000-6-4 Standard emisije za stambene, poslovne i lake industrijske sredine conforming to IEC 61000-6-3 Otpornost za industrijske sredine conforming to IEC 61000-6-2
Standardi	IEC 60255-1
Sertifikacija proizvoda	GOST[RETURN]CSA[RETURN]GL[RETURN]C-Tick[RETURN]UL
Direktive	89/336/EEC - elektromagnetna kompatibilnost 73/23/EEC - niskonaponska direktiva
Temperatura okoline za skladištenje	-40...70 °C
Temperatura okoline za rad	-20...50 °C
Relativna vlažnost	95 % pri 55 °C u skladu sa IEC 60068-2-30
Otpornost na vibracije	0.35 mm (f= 5...57,6 Hz) u skladu sa IEC 60068-2-6 1 gn (f= 57,6...150 Hz) u skladu sa IEC 60255-21-1
Otpornost na udare	15 gn za 11 milisekundi u skladu sa IEC 60255-21-1
Ip stepen zaštite	IP20 u skladu sa IEC 60529 (priključci) IP30 u skladu sa IEC 60529 (kućište)
Stepen zaprljanosti	3 u skladu sa IEC 60664-1
Dielektrični test napon	2 kV AC 50 Hz, 1 min u skladu sa IEC 60255-5 2 kV AC 50 Hz, 1 min u skladu sa IEC 60664-1
Nerasut udarni talas	4 kV u skladu sa IEC 60255-5 4 kV u skladu sa IEC 60664-1 4 kV u skladu sa IEC 61000-4-5

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2,800 cm
Package 1 Width	7,800 cm
Package 1 Length	9,600 cm
Package 1 Weight	92,000 g
Unit Type of Package 2	S02

Number of Units in Package 2	48
Package 2 Height	15,000 cm
Package 2 Width	30,000 cm
Package 2 Length	40,000 cm
Package 2 Weight	4,935 kg

Održivost ponude


Status održive ponude	Green Premium proizvod
Propis REACh	 REACh Deklaracija
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	 Informacije O Kraju Radnog Veka

Ugovorna garancija

Garancija	18 meseci
-----------	-----------


Multifunction 3-Phase Supply Control Relays

Dimensions and Mounting




Multifunction 3-Phase Supply Control Relays

Wiring Diagram



Function Diagram

Phase Sequence Control, Phase Failure Detection ($U_{\text{measured}} < 0.7 \times \text{nominal supply voltage}$), and Asymmetry Detection



Legend

Tt Time delay after crossing of threshold

L1, L2, L3 Phases of the supply voltage monitored

A Asymmetry threshold

H Hysteresis

11-12, 11-14 Output relay connections

Relay status: black color = energized.