



### Osnovne informacije

Grupa proizvoda	Compact
Ime proizvoda	Compact NSX
Grupa proizvoda	ComPact NSX100...250
Kratko ime uređaja	NSX250N
Tip proizvoda ili komponente	Prekidač
Primena uređaja	Razvod električne energije
Number of poles	3P
Opis zaštićenih polova	3t
[in] nazivna struja	160 A at 40 °C
[ue] nazivni napon	690 V AC 50/60 Hz
Tip mreže	AC
Mrežna frekvencija	50/60 Hz
Pogodno za izolaciju	Yes conforming to EN/IEC 60947-2
Kategorija upotrebe	Kategorija A
[Icu] rated ultimate short-circuit breaking capacity	85 KA at 240 V AC 50/60 Hz conforming to UL 508 10 KA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 35 KA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 50 KA at 480 V AC 50/60 Hz conforming to UL 508 36 KA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 50 KA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 50 KA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 90 KA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 15 kA at 600 V AC 50/60 Hz conforming to UL 508
Performance level	N 50 kA 415 V AC
Ime zaštitne jedinice	Micrologic 2.2
Tehnologija zaštitne jedinice	Elektronska
Funkcija zaštitne jedinice	LSol
Tip upravljanja	Ručica
Circuit breaker mounting mode	Fiksno

Informacije navedene u ovoj dokumentaciji predstavljaju opšti opis odnosno tehničke karakteristike performansi proizvoda. Dokumentacija nije namenjena da bude zamena za niti se može koristiti za određivanje prikladnosti i pouzdanosti proizvoda za specifičnu krajnju primenu. Dužnost je korisnika odnosno integratora da izvrši primerenu i sveobuhvatnu analizu rizika, procenu i proveru proizvoda u pogledu odgovarajuće specifične primene ili načina korišćenja. Ni Schneider Electric Industries SAS ni njegova povezana ili zavisna društva neće snositi odgovornost za zloupotrebu ovenavedenih informacija.

## Dopunske informacije

[ui] nazivni napon izolacije	800 V AC 50/60 Hz
[uimp] nazivni podnosivi impulsni napon	8 kV
[Ics] rated service short-circuit breaking capacity	10 KA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 35 KA at 525 V AC 50/60 Hz conforming to IEC 60947-2 36 KA at 500 V AC 50/60 Hz conforming to IEC 60947-2 50 KA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 50 KA at 440 V AC 50/60 Hz conforming to IEC 60947-2 90 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2
Mehanička trajnost	20000 ciklusa
Električna trajnost	5000 Cycles at 690 V In 10000 Cycles at 690 V In/2 10000 Cycles at 440 V In 20000 cycles at 440 V In/2
Nosači za montažu	Zadnja ploča
Gornji priključak	Prednja
Donji priključak	Prednji
Povezivanje	35 mm
Tip zaštite	L : for overload protection (long time) So : for short time short-circuit protection with fixed delay I : for instantaneous short-circuit protection
Veličina zaštitne jedinice	160 A at 40 °C
Long-time pick-up adjustment type Ir (thermal protection)	Podesivo 9 podešavanja
[Ir] long-time protection pick-up adjustment range	63...160 A
Long-time protection delay adjustment type tr	Fiksno
[tr] long-time protection delay adjustment range	11 S at 7.2 x Ir 16 S at 6 x Ir 400 s at 1.5 x Ir
Termička memorija	20 minuta pre i nakon okidanja
Short-time protection pick-up adjustment type Isd	Podesivo, 9 podešavanja
[Isd] Short-time protection pick-up adjustment range	1.5...10 x Ir
Short-time protection delay adjustment type tsd	Fiksno
Instantaneous protection pick-up adjustment type li	Fiksno
[li] instantaneous protection pick-up adjustment range	2400 A
Diferencijalna zaštita	Bez
Zona selektivne blokade zsi	Bez
Number of slots for electrical auxiliaries	5 slot(s)
Lokalna signalizacija	Flashing LED (green) for ready to operate LED 105 % Ir (red) for overload LED 90 % Ir (orange) for overload
Width (W)	105 mm
Height (H)	161 mm
Depth (D)	86 mm
Masa proizvoda	2,4 kg

## Okruženje

Standardi	EN/IEC 60947
Sertifikacija proizvoda	CCC EAC Marine
Kategorija prenapona	Klasa II
Klasa zaštite od električnog udara	Klasa II
Stepen zaprljanosti	3 conforming to IEC 60664-1
Ip stepen zaštite	IP40 conforming to IEC 60529
Ik stepen zaštite	IK07 conforming to IEC 62262
Temperatura okoline za rad uređaja	-25...70 °C
Temperatura okoline za skladištenje	-50...85 °C

Relativna vlažnost	0...95 %
Nadmorska visina za rad uređaja	0...2000 m without derating 2000 m...5000 m with derating

### Packing Units

Tip jedinice pakovanja 1	PCE
Broj jedinica u pakovanju 1	1
Pakovanje 1 težina	1,963 kg
Pakovanje 1 visina	11 cm
Pakovanje 1 širina	13,5 cm
Pakovanje 1 dužina	19 cm

### Offer Sustainability

Status održive ponude	Green Premium proizvod
Propis REACH	<a href="#">REACH Deklaracija</a>
EU RoHS direktiva	Usaglašeno <a href="#">EU RoHS Deklaracija</a>
Bez žive	Da
Informacije o RoHS izuzecima	<a href="#">Da</a>
RoHS regulativa za Kinu	<a href="#">RoHS Deklaracija Za Kinu</a>
Izjava o zaštiti okoliša	<a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>
Profil cirkularnosti	<a href="#">Informacije O Kraju Radnog Veka</a>
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

### Contractual warranty

Garancija	18 meseci
-----------	-----------