

Tehničke karakteristike proizvoda

Karakteristike

XB7NS9445

nužno isključenje Ø 22-crvena pečurk. glava Ø 40mm-otpuštanje ključem-1 NO+1 NC



Osnovne informacije

Grupa proizvoda	Harmony XB7
Tip proizvoda ili komponente	Taster za nužno isključenje
Kratko ime uređaja	XB7
Prečnik za montiranje	22 mm
Prodaja po nedeljivim količinama	10
Oblik glave signalne jedinice	Okrugla
Tip glave uređaja	zadržka
Reset	Otpuštanje ključem
Profil glave uređaja	Crvena pečurkasti taster Ø 40 mm, neoznačeno
Tip brave	Key 455
Tip kontakata i sastav	1 NO + 1 NC
Povezivanje - priključci	Vijčani priključni blokovi, $\leq 2 \times 1.5 \text{ mm}^2$ sa kablovskim završetkom u skladu sa IEC 60947-1 Vijčani priključni blokovi, $1 \times 0.34...2 \times 2.5 \text{ mm}^2$ bez kablovskog završetka u skladu sa IEC 60947-1
Prezentacija uređaja	Monolitni proizvod

Dopunske informacije

Cad ukupna širina	40 mm
Cad ukupna visina	40 mm
Cad ukupna dubina	72 mm
Opis priključaka iso n°1	(21-22)NC (13-14)NO
Masa proizvoda	0,035 kg
Montaža uređaja	Otvor za montažu - prečnik: 22,5 mm 22.3 +0.4/0 u skladu sa IEC 60947-1
Centar za fiksiranje	$\geq 30 \times 40 \text{ mm}$ (nosač panela) metal 1...6 mm $\geq 30 \times 40 \text{ mm}$ (nosač panela) plastika 2...6 mm
Način fiksiranja	Maticom za fiksiranje ispod glave: 2...2,4 N.m
Operacija kontakata	Trenutno delovanje
Upotreba kontakata	Standardni
Pozitivno otvaranje	Sa u skladu sa IEC 60947-5-1 dodatak K
Mehanička trajnost	100000 ciklusa
Moment pritezanja	0,8...1,2 N.m u skladu sa IEC 60947-1
Oblik glave zavrtnja	Ukrštena kompatibilno sa JIS No 1 odvijač Ukrštena kompatibilno sa Philips no 1 odvijač Ukrštena kompatibilno sa pozidriv No 1 odvijač Sa prerezom kompatibilno sa matica Ø 4 mm odvijač Sa prerezom kompatibilno sa matica Ø 5.5 mm odvijač
Zaštita od kratkog spoja	4 A rastavni uložak tip gG u skladu sa IEC 60947-5-1
[ui] nazivni napon izolacije	250 V (stepen zaprljanosti 3) u skladu sa IEC 60947-1
[uimp] nazivni podnosivi impulsni napon	4 kV u skladu sa IEC 60947-1
[ie] nazivna radna struja	0,1 A pri 250 V, DC-13, R300 u skladu sa IEC 60947-5-1 0,22 A pri 125 V, DC-13, R300 u skladu sa IEC 60947-5-1 0,75 A pri 240 V, AC-15, C300 u skladu sa IEC 60947-5-1 1,5 A pri 120 V, AC-15, C300 u skladu sa IEC 60947-5-1

Električna trajnost	1000000 Ciklusa, DC-13, 0,3 A pri 24 V, broj operacija <216000 ciklusa/min, faktor opterećenja: 0,5 u skladu sa IEC 60947-5-1 dodatak C 1000000 Ciklusa, AC-15, 0,03 A pri 230 V, broj operacija <216000 ciklusa/min, faktor opterećenja: 0,5 u skladu sa IEC 60947-5-1 dodatak C 1000000 ciklusa, AC-15, 0,09 A pri 240 V, broj operacija <108000 ciklusa/min, faktor opterećenja: 0,5 u skladu sa IEC 60947-5-1 dodatak C
Električna pouzdanost iec 60947-5-4	$\Lambda < 5 \times 10\exp(-7)$ pri 17 V i 5 mA u skladu sa IEC 60947-5-4

Okruženje

Tretman zaštite	TH
Temperatura okoline za skladištenje	-40...70 °C
Temperatura okoline za rad uređaja	-25...70 °C
Klasa zaštite protiv električnog udara	Klasa II u skladu sa IEC 60536
Ip stepen zaštite	IP20 u skladu sa IEC 60529 (zadnji deo) IP65 u skladu sa IEC 60529 (prednji deo)
Nema stepen zaštite	NEMA 12 u skladu sa UL 50 NEMA 3 u skladu sa UL 50
Standardi	IEC 60947-5-5 IEC 60364-5-53 ISO 13850 IEC 60947-1 IEC 60947-5-1 CSA C22.2 No 14 UL 508 IEC 60204-1
Sertifikacija proizvoda	CCC[RETURN]GOST
Otpornost na vibracije	5 gn (f= 2...500 Hz) u skladu sa IEC 60068-2-6
Otpornost na udare	15 gn (trajanje = 11 milisekundi) za ubrzanje polovine sinusne periode u skladu sa IEC 60068-2-27

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15,0 cm
Package 1 Width	16,0 cm
Package 1 Length	8,0 cm
Package 1 Weight	75,0 g
Unit Type of Package 2	BAG
Number of Units in Package 2	10
Package 2 Height	16,0 cm
Package 2 Width	15,0 cm
Package 2 Length	8,0 cm
Package 2 Weight	758,0 g
Unit Type of Package 3	S01
Number of Units in Package 3	50
Package 3 Height	15 cm
Package 3 Width	15 cm
Package 3 Length	40 cm
Package 3 Weight	4,151 kg

Održivost ponude


Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)  EU RoHS deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu

Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	 Informacije O Kraju Radnog Veka
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija


Garancija	18 meseci
-----------	-----------

Non-illuminated Pushbutton




Mounting

Diameter of Finished Fixing Holes



- (1) Minimum value.
- (2) 40 mm/1.58 in. for Emergency switching off pushbutton only.
- (3) Standard value: Ø 22.3 (0; + 0.4) mm/Ø 0.88 (0; + 0.02) in.

“U” Type Tag Connection



- (1) 6.5 mm/0.26 in. recommended, 7 mm/0.28 in. max.
- (2) M3 screw clamp terminal.

Wiring

