

Tehničke karakteristike proizvoda

Karakteristike

XBKT50000U11M

Zelio Count brojač impulsa - mehanički displej
5 cifara - 115 V AC



Osnovne informacije

Grupa proizvoda	Zelio Count
Tip proizvoda ili komponente	Brojač
Tip displeja	Mehanička
Veličina	31 x 41.5 mm
Cifre na displeju	5 cifra(e)
Frekvencija brojača	10 Hz
Reset	Ručni
Kapacitet brojanja	0...99999
Vrsta tehnologije	Elektromehanička

Dopunske informacije

[us] nazivni napon napajanja	115 V AC 50/60 Hz Us +/- 10 %
Potrošnja	2,5 W
Vreme čuvanja podataka	Trajno
Tip brojača	Dodavanje
Funkcija ulaza	Brojanje
Tip ulaza	Kontakt
Mehanička trajnost	10000000 ciklusa
Način montiranja	Ugradno
Nosači za montažu	Panel za montažu
Povezivanje - priključci	AMP papučice (kutija za povezivanje)
Visina	31 mm
Masa proizvoda	0,1 kg
Širina	41,5 mm
Namena proizvoda	Kabl
Veličina teksta	4 mm

Okruženje

Standardi	EN 50081-2 EN 50082-2
Sertifikacija proizvoda	cUR
Ip stepen zaštite	IP40 u skladu sa EN/IEC 60529
Temperatura okoline za rad uređaja	-10...50 °C
Temperatura okoline za skladištenje	-20...60 °C
Otpornost na vibracije	5 gn (f= 10...150 Hz) u skladu sa EN/IEC 60068-2-6
Otpornost na udare	30 gn za 6 milisekundi u skladu sa EN/IEC 60068-2-27
Klasa zaštite protiv električnog udara	Klasa II u skladu sa IEC 60536

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4,3 cm
Package 1 Width	4,8 cm
Package 1 Length	9 cm
Package 1 Weight	100 g

Održivost ponude

EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	18 meseci
-----------	-----------

Electromechanical and Electronic Totalizing Counters


Dimensions, Flush-Mounting

Counters Dimensions	Flush-Mounting
XBKT50000U••M, XBKT70000U••M	
XBKT60000U00M	
XBKT60000U1•M	
XBKT80000U00M	
XBKT81030U33E	
e: panel thickness, 1 mm < e < 2.5 mm / 0.039 in. < e < 0.098	


Wiring Diagrams of Electromechanical and Electronic Totalizing Counters

Counters with Mechanical Display

XBKT50000U••M, XBKT70000U00M




XBKT60000U1•M, XBKT80000U00M



Counters with LCD Display, Lithium Battery Supply

XBKT181030U33E

PNP Transistor, NPN Transistor




- 1: Keylock
- 2: 0 V
- 3: Count
- 4: Reset

Reset Key Locking Facility



- 1: Keylock
- 2: 0 V
- 3: Count
- 4: Reset

Volt-free Contact



- 1: Keylock
- 2: 0 V
- 3: Count
- 4: Reset