

Tehničke karakteristike proizvoda

Karakteristike

XVC6B4

60mm svetlosna kolona CNZP na dršci



Osnovne informacije

Grupa proizvoda	Harmony XVC6
Tip proizvoda ili komponente	Kompletno ožičena monolitna svetleća kolona
Tip baze svetleće kolone ili semafora	4 svetleće jedinice
Zvučni signal	Bez
Prečnik za montiranje	60 mm
Ime komponente	XVC
Svetlosni izvor	LED trajna crvena LED trajna narandžasta LED trajna zelena LED trajna plava
[us] nazivni napon	24 V
Tip kola napajanja	AC/DC

Dopunske informacije

Materijal	Polikarbonat: svetleća jedinica ABS (akrilonitril-butadien-stiren): bazi PBT + ABS (UL94HB): gornji poklopac STK (hromiran): cevasti nosač
Montaža proizvoda	Na cevnom nosaču, 22 mm
Poprečni presek kabla	0,33 mm ²
Awg mera (američki standard za prečnik žice)	AWG 22
Dužina kabla	600 mm
Označavanje	CE
[uimp] nazivni napon impulsa	0,8 kV
Struja potrošnje	100 mA
Frekvencija treptanja	1 Hz
Masa proizvoda	0,82 kg
Visina	548,3 mm

Okruženje

Standardi	IEC 61000-6-3 IEC 61000-6-4 IEC 61000-6-2
Sertifikacija proizvoda	UL
Tretman zaštite	TC
Temperatura okoline za skladištenje	-35...70 °C
Temperatura okoline za rad uređaja	-10...50 °C
Klasa zaštite protiv električnog udara	Klasa I u skladu sa IEC 61140
Ip stepen zaštite	IP23 instalaciji na vertikalnu površinu u skladu sa IEC 60529

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8,500 cm
Package 1 Width	8,500 cm
Package 1 Length	77,500 cm
Package 1 Weight	1,112 kg
Unit Type of Package 2	P06
Number of Units in Package 2	10
Package 2 Height	45,000 cm
Package 2 Width	60,000 cm
Package 2 Length	80,000 cm
Package 2 Weight	20,984 kg

Održivost ponude

EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Izjava o zaštiti okoliša	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Informacije O Kraju Radnog Veka


Ugovorna garancija

Garancija	18 meseci
-----------	-----------

Pre-assembled and Pre-wired Tower Light with Support Tube Mounting

Dimensions

Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get b dimension.



No. of illuminated units	b Without buzzer (mm)	b Without buzzer (in.)
1 stage	428.3	16.86
2 stages	468.3	18.44
3 stages	508.3	20.01
4 stages	548.3	20.01
5 stages	588.3	23.16

Pre-assembled and Pre-wired Tower Light

Support Tube Mounting

